


Features

- Trench Power LV MOSFET technology
- High Power and current handling capability



Application

- PWM application
- Load switch



Product Summary

V_{DS}	$R_{DS(ON)} \text{ MAX}$	$I_D \text{ MAX}$
20V	250mΩ@4.5V	1.2A
	350mΩ@2.7V	



Schematic diagram



Halogen-Free

Absolute Maximum Ratings (TA=25°C unless otherwise noted)

Symbol	Parameter	Rating	Unit
--------	-----------	--------	------

Common Ratings (TC=25°C Unless Otherwise Noted)







V _{DS}	Drain-Source Breakdown Voltage		20	V
V _{GS}	Gate-Source Voltage		±12	V
T _J	Maximum Junction Temperature		150	°C
T _{STG}	Storage Temperature Range		-50 to 155	°C
I _S	Diode Continuous Forward Current	Tc=25°C	1.2	A


Mounted on Large Heat Sink

I_{DM}	Pulse Drain Current Tested	$T_C=25^\circ\text{C}$	7.4	A
I_D	Continuous Drain Current	$T_C=25^\circ\text{C}$	1.2	A
P_D	Maximum Power Dissipation	$T_C=25^\circ\text{C}$	0.54	W
$R_{\theta JA}$	Thermal Resistance Junction-to-Ambient		230	°C/W

Electrical Characteristics (T _J =25°C unless otherwise noted)						
Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
BV _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250μA	20	--	--	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =20V, V _{GS} =0V	--	--	1	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±12V, V _{DS} =0V	--	--	±100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	0.5	--	--	V
R _{DS(on)}	Drain-Source On-State Resistance	V _{GS} =4.5V, I _D =0.93A	--	--	250	mΩ
		V _{GS} =2.7V, I _D =0.47A	--	--	350	mΩ
Dynamic Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
C _{ISS}	Input Capacitance	V _{DS} =10V, V _{GS} =0V, f=1MHz	--	200	--	pF
C _{OSS}	Output Capacitance		--	35	--	pF
C _{RSS}	Reverse Transfer Capacitance		--	28	--	pF
Switching Characteristics						
Q _g	Total Gate Charge	V _{DS} =10V, I _D =1.2A, V _{GS} =4.5V	--	3	--	nC
Q _{gs}	Gate Source Charge		--	0.5	--	nC
Q _{gd}	Gate Drain Charge		--	0.7	--	nC
t _{d(on)}	Turn-on Delay Time	V _{DD} =10V, I _D =1.2A, V _{GS} =4.5V, R _G =3Ω	--	3	--	nS
t _r	Turn-on Rise Time		--	11	--	nS
t _{d(off)}	Turn-Off Delay Time		--	20	--	nS
t _f	Turn-Off Fall Time		--	8	--	nS
Source- Drain Diode Characteristics						
V _{SD}	Forward on voltage	T _J =25°C, I _S =1.2A	--	--	1.2	V

Typical Operating Characteristics



SOT-23 Package information


Symbol	Dimensions in Millimeters(mm)		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E1	2.250	2.550	0.088	0.100
E	1.200	1.400	0.047	0.055
e	0.950TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°