




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.64 mm [.025 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.64 mm[.025 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	.7 – 10.2 kgf

Dimensions

Product Length	22.5 mm[.886 in]
Compatible Insulation Diameter Range	2.29 – 3.94 mm[.09 – .155 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



KIT

REPRESENTATION ONLY


TE Part # 7-2150135-7
[OCEAN_2.0_SPARE_PART_KIT-110F180F](#)



TE

TE Part # 2150135-2
[OCEAN-2.0-APPLICATOR-E-110F180F-REA](#)

Also in the Series | Mark II



[Automotive Connector Locks & Position Assurance\(1\)](#)




[Automotive Housings\(6\)](#)



[Automotive Terminals\(1\)](#)



[Connector Seals & Cavity Plugs\(1\)](#)



[Crimp Terminal Housings\(178\)](#)




[Insertion & Extraction Tools\(3\)](#)




[Quick Disconnects\(174\)](#)

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(178)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(5)



Quick Disconnects(174)

Customers Also Bought



TE Part #320562
SPLICE BUTT PIDG 16-14



TE Part #154719-1
250 HSG. PL MKI REC. NAT



TE Part #DT6P-DC
PROTECT CVR, 6P, REC, GRY, DT



TE Part #2-1418390-1
4 POS AMP MCP 2.8 REC HSG



TE Part #63097-1
250 PL MKII REC. 18-14AWG TPBR




TE Part #60295-2
FF 250 REC 22-18AWG TPBR



TE Part #280755-4
FF 375 REC 6-10MM2 TPPB



TE Part #2292906-1
2POS,MCON 1.2,REC HSG ASSY,SLD, COD A



TE Part #282438-1
MINI MIC SRS REC CONT HYBRD



TE Part #62638-1
RING TONGUE 22-20 AWG TPBR

Documents



Product Drawings

PL 250 TERMINAL REC 18-14 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_63809-1_F.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63809-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63809-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English