



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
PCB Thickness (Recommended): **1.57 mm [.062 in]**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.8 mm [.031 in]**
PCB Hole Diameter: **1.4 mm [.055 in]**

Features

Product Type Features

Terminal Features	Stud Hole
-------------------	-----------

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 μm[150 μin]
Contact Underplating Material Thickness	1.27 μm, 2.54 μm[50 μin][100 μin]
Contact Mating Area Plating Material Thickness	3.81 μm[150 μin]
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.8 mm[.031 in]
Terminal Plating Material	Tin
Contact Underplating Material	Copper, Nickel
Terminal Size	6.35
Terminal Orientation	Straight

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------



Product Terminates To	Printed Circuit Board
Mechanical Attachment	
Wire Insulation Support	With

Dimensions	
Extension Below Board	4.57 mm[.18 in]
Stud Diameter	1.71 mm
Terminal Material Thickness	.8 mm[.032 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
PCB Hole Diameter	1.4 mm[.055 in]
Profile Height from PCB	10.21 mm[.402 in]

Usage Conditions	
Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features	
Packaging Quantity	10000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1217539-1 250 FASTON,PCB TAB,TCBR	 TE Part # 63950-1 250 FASTON TAB TPBR	 TE Part # 1217125-1 250 FASTON,PCB TAB,TPBR	 TE Part # 1217127-1 250 FASTON,PCB TAB,TPBR
 TE Part # 1217136-3 250 FASTON,PCB TAB,TNBR	 TE Part # 63862-2 250 FASTON TAB TPBR	 TE Part # 63950-6 FASTON 250 PCB TAB BR	 TE Part # 1217566-2 250 FASTON,PCB TAB,TCBR
 TE Part # 1217861-1 250 FASTON,PCB TAB,TCBR	 TE Part # 63949-1 250 FASTON TAB TPBR	 TE Part # 1217126-1 250 FASTON,PCB TAB,TPBR	 TE Part # 1217566-1 250 FASTON,PCB TAB,TCBR

Also in the Series | FASTON 250

 Compression Connectors(4)	 Crimp Terminal Housings(118)	 Insertion & Extraction Tools(6)	 Insulation Boots & Sleeves(16)
-------------------------------	----------------------------------	-------------------------------------	------------------------------------



Magnet Wire Terminals(1)



PCB Terminals(133)



Quick Disconnects(425)




Splices(4)

Customers Also Bought




TE Part #177921-1
POWER D/LOCK PLATE 5P NATURAL



TE Part #521781-1
250 HSG. PL MKIII REC. 6.81mm 4P NAT



TE Part #1-1658623-0
50 NOVO MIL 30DP, LEAD FREE




TE Part #7-2377775-1
GI2.5 TPA,7P



TE Part #2-1971798-4
NEW GI CONN2.5 HDR ASMBLY 2P YLW D1.0



TE Part #5102154-7
A/L UNIV HDR 30P VERT



TE Part #179970-1
250 HSG. PL EX REC.



TE Part #3-641216-4
04P MTA100 HDR ASSY FL/RA LF



TE Part #1217113-2
187 PL MKIII REC. 22-18AWG TPBR



TE Part #776262-4
14POS,PIN DIA 1.3,HDR ASSY, 180DEG,COD 4

Documents

Product Drawings

250 FASTON,PCB TAB,TNBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1217136-1_J_c-1217136-1-j.2d_dxf.zip

1217136-1

Tab, 6.35 mm [.25 in] Tab Width, 1.4 mm [.055 in] PCB Hole, Through Hole - Solder, Tin Plating, Reel, FASTON 250, PCB Terminals



English

Customer View Model

[ENG_CVM_CVM_1217136-1_J_c-1217136-1-j.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1217136-1_J_c-1217136-1-j.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON PCB Tabs and Receptacles](#)

English

[PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English