


12.95 [0.510]















 $\langle 15.75 \text{ } [0.620] \rangle$ 

Code: A~Z

XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.08.22

Code List:

Colde							
	A	B	C	D	E	F	G
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Grey/7031
PART NO.	XK1PLF1S3-NA36-A	XK1PLF1S3-NA36-B	XK1PLF1S3-NA36-C	XK1PLF1S3-NA36-D	XK1PLF1S3-NA36-E	XK1PLF1S3-NA36-F	XK1PLF1S3-NA36-G
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.	Violet/4003	Beige/1001	Curry/1027	Carmine red/3002	Pastel Orange/2003	Pastel Green/6019	Water Blue/5021
PART NO.	XK1PLF1S3-NA36-H	XK1PLF1S3-NA36-I	XK1PLF1S3-NA36-K	XK1PLF1S3-NA36-L	XK1PLF1S3-NA36-M	XK1PLF1S3-NA36-N	XK1PLF1S3-NA36-Z

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: FAKRA Female Connector for RG174
CHECKED		UNIT: mm/in	PART NO.: XK1PLF1S3-NA36-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLF1S3-NA36-X
			SCALE: N/A
			PAGE: 2/2
			REVISION: A0

NOTE: ALL RIGHTS RESERVED,BANNED COPY!