





This document is the property of Amphenol Corporation and is delivered on the understanding that it contains neither recommendations nor instructions in relation to any patent, for manufacture or use by anyone other than Amphenol Corporation. It is to be used for reference only and is not to be reproduced or to be used for any information in this document.



15 pos.
Drawing for sub-assembly
L17DPPK15JS

15 pos.
Plastic shell



15 pos.
Drawing for side
L17DPPK15JS

VARIANT OF CABLE
STRAIN RELIEF
thumb
screw

Customer drawing

Commercial Part Number	Dimension				
	A	B	C	D	E
L 17D PPK 09 JS	31.5	18	15	34	49
L 17D PPK 15 JS	40	26	15	34	49
L 17D PPK 25 JS	53.5	28	15	40	49
L 17D PPK 37 JS	71	55	16	40	49



REVISIONS			
SYM	ECN	DESCRIPTION	DATE
A	HK4729	Release new drawing	10/19/07

D-SUB TECHNICAL DATA

Material and finish:

Shell: Thermoplastic, UL94-V0 color black
Thumb screws: Steel shaft with plastic knob, blue chromate plated
Screws: Steel, blue chromate plated, Philips head
Strain relief: Steel, blue chromate plated
cable clamp with self-tapping screws
Cover: Thermoplastic, UL94-V0 colour black
Temperature range: -40°C to 120°C
Attenuation factor: >40 dB between 30 MHz and 1 GHz

PRODUCT CODE

L 17DPPK XX JS



RoHS Compliance

Series: 17DPPK



Position: 09,15,25,37

UNLESS OTHERWISE SPECIFIED			APPROVAL		DATE	
TOLERANCES			DRAWN	Iss. prng	10/17/07	
U.S.			CHECKED	14. using	10/17/07	
.X +/-	0.50					
.XX +/-	0.30					
.XXX +/-	0.20					
FRACTIONS +/-	5"					
ANGLES +/-	5°					
REMOVE SHARP EDGES			DRAWING FILE : (Drawing) Hood C17DPPK15JS			
DIMENSIONS			ANGLE OF PROJECTION			
U.S.	INCHES					
MM						
TITLE						
Hood, DPPK Series						
SIZE DRAWING NO.						
A4 C L17D PPK XXJS						
SCALE NONE			SHEET 1 OF 3			
			REV. A			

This document is the property of Amphenol Corporation and is delivered on the understanding that it is not to be reproduced, stored in a retrieval system or in part, for manufacture or use by anyone other than the intended recipient. It is loaned to the recipient and it is not to be distributed or to use any information in this document.



25 pos.
Drawing for sub-assembly
L17DPPK25JS
25 pos.
Plastic shell



25 pos.
Drawing for side
L17DPPK25JS
2
Screw
Strain relief
Cover

Customer drawing

Commercial Part Number	Dimension				
	A	B	C	D	E
L 17D PPK 09 JS	31.5	18	15	34	49
L 17D PPK 15 JS	40	26	15	34	49
L 17D PPK 25 JS	53.5	28	15	40	49
L 17D PPK 37 JS	71	55	16	40	49



REVISIONS			
SYM	ECN	DESCRIPTION	DATE
A	HK4729	Release new drawing	10/19/07

D-SUB TECHNICAL DATA


Material and finish:
Shell: Thermoplastic, UL94-V0 color black
Thumb screws: Steel shaft with plastic knob, blue chromate plated
Screws: Steel, blue chromate plated, Philips head
Strain relief: Steel, blue chromate plated cable clamp with self-tapping screws
Cover: Thermoplastic, UL94-V0 colour black
Temperature range: -40°C to 120°C
Attenuation factor: >40 dB between 30 MHz and 1 GHz

PRODUCT CODE


L 17DPPK XX JS
RoHS Compliance
Series: 17DPPK
Position: 09,15,25,37

UNLESS OTHERWISE SPECIFIED				APPROVAL		DATE	
TOLERANCES				DRAWN	Iss. prng	10/17/07	
U.S.				CHECKED	14. using	10/17/07	
X +/-				0.50			
XX +/-				0.30			
FRACTIONS +/-				0.20			
ANGLES +/-				5°			
FOR MATERIALS AND FINISHES				DRAWING FILE :			
SEE NOTES				Drawing Date: 10/17/07			
REMOVE SHARP EDGES				ANGLE OF PROJECTION			
DIMENSIONS				TITLE			
U.S. INCHES				Hood, DPPK Series			
MM				SIZE: DRAWING NO. A4			
				C L17D PPK XXJS			
				SCALE NONE			
				SHEET 2 OF 3			

This document is the property of Amphenol Corporation and is delivered on the understanding that it contains confidential information and is not to be reproduced, stored in a retrieval system, or used in any form, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation. If you are not an authorized recipient, you are notified that disclosing, copying, distributing or taking any action in reliance on the contents of this information is strictly prohibited or to use any information in this document.



09/37 pos.
Drawing for sub-assembly
L17DPPK09JS/L17DPPK37JS



09/37 pos.
Drawing for side
L17DPPK09JS/L17DPPK37JS

Customer drawing

Commercial Part Number	Dimension				
	A	B	C	D	E
L 17D PPK 09 JS	31.5	18	15	34	49
L 17D PPK 15 JS	40	26	15	34	49
L 17D PPK 25 JS	53.5	28	15	40	49
L 17D PPK 37 JS	71	55	16	40	49



REVISIONS			
SYM	ECN	DESCRIPTION	DATE
A	HK4729	Release new drawing	10/19/07
APPROVED			IP

D-SUB TECHNICAL DATA

Material and finish:
Shell: Thermoplastic, UL94-V0 color black
Thumb screws: Steel shaft with plastic knob, blue chromate plated
Screws: Steel, blue chromate plated, Philips head
Strain relief: Steel, blue chromate plated cable clamp with self-tapping screws
Cover: Thermoplastic, UL94-V0 colour black
Temperature range: -40°C to 120°C
Attenuation factor: >40 dB between 30 MHz and 1 GHz

PRODUCT CODE

L 17DPPK XX JS

RoHS Compliance

Series: 17DPPK

Position: 09,15,25,37

UNLESS OTHERWISE SPECIFIED				APPROVAL		DATE		TITLE	
TOLERANCES		U.S.		DRAWN	Iss. prng	10/17/07	10/17/07		
±	±	0.50		CHECKED	14. using			Amphenol	
FRACTIONS ±	±	0.20							
ANGLES ±	±	5°						Hood, DPPK Series	
REMOVE SHARP EDGES									
FOR MATERIALS AND FINISHES SEE NOTES			DRAWING FILE : (Drawing Name)C17DPPKXXJS					SIZE DRAWING NO.	
DIMENSIONS			ANGLE OF PROJECTION					SCALE	
								NONE	
								SHEET 3 OF 3	
								REV.	
								A	
			</						