

T1240100116-000  ACTIVE

HDC | HDC IP65

TE Internal #: T1240100116-000

Heavy Duty Connector Hood, Top & Side Entry, Locking Clip,
Sealable, HDC IP65

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Top & Side**

Hood & Base Locking Device Type: **Locking Clip**

Sealable: **Yes**

Features

Product Type Features

Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Cable Entry Location	Top & Side
----------------------	------------

Mechanical Attachment

Thread Size	PG16
Hood & Base Locking Device Type	Locking Clip

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1410102000-000
H10B-AG



TE Part # T1750102116-000
H10B-TBFH-PG16



TE Part # T2040102101-000
HE-010-M




TE Part # T1410101000-Y00
H10B-AGS,MINERAL OIL RESISTANCE




TE Part # T3609160101-000
DLX-16-MS


Also in the Series | **HDC IP65**



Connector Caps & Covers(25)

Rectangular Connector Hoods & Bases
(1232)

Customers Also Bought

TE Part #828905-1
SINGLE-WIRE-SEAL(5MM HOLE)TE Part #1743064-2
MT-2/JPT SLD 36P PLUG COVER BKTE Part #828985-1
RUBBER PLUG >2,5-4,0MM2TE Part #280756-2
FF 375 REC 3-6MM2 TPBRTE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TABTE Part #963530-1
EINZELLEITERDICHTUNGTE Part #1743636-2
HYB SLD 36P CAP HSGTE Part #1393240-7
RT314730TE Part #235304-1
HOUSING 375 SRS FI/FO TAB

Documents

Product Drawings

[H10B-TGH-PG16](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_T1240100116-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1240100116-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1240100116-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

[HEAVY DUTY CONNECTORS](#)

Japanese

Product Specifications

[Application Specification](#)

English