



















1		2		3		4																																																																
ROHS		 3D View		<table><tr><th colspan="6">REVISIONS</th></tr><tr><th>REV.</th><th>ECN NO.</th><th>LOCATION</th><th>DESCRIPTION</th><th>DATE</th><th>DESIGN</th></tr><tr><td>A0</td><td>N/A</td><td></td><td>INITIAL RELEASE</td><td>2024.09.02</td><td></td></tr></table>				REVISIONS						REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN	A0	N/A		INITIAL RELEASE	2024.09.02																																														
REVISIONS																																																																						
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN																																																																	
A0	N/A		INITIAL RELEASE	2024.09.02																																																																		
 11.10 [0.437] 9.58 [0.377]				Specifications(规格): 1.Impedance(特性阻抗): 50Ω; 2.Frequency (工作频率): DC~3GHz; 3.VSWR (电压驻波比): 1.50 Max. 4.Insulation resistance(绝缘阻抗): ≥100MΩ; 5 Dielectric withstand voltage (介质耐电压): 800V AC; 6.Mating cycles (耐久性): ≥10 cycles; 7.Engagement force(啮合力): ≤60N; 8.Retention force latch(保持力): ≥110N; 9.Temperature range(使用温度): -40℃~+105℃; PART NO.: XMOTLF4S3-NJ06-X Code: A~Z																																																																		
 4.00 [0.157]		 18.80 [0.740]																																																																				
 4.00 [0.157]				<table><tr><th colspan="6">BOM List:</th></tr><tr><td>①</td><td>②</td><td>③</td><td>④</td><td>⑤</td><td>⑥</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>				BOM List:						①	②	③	④	⑤	⑥																																																			
BOM List:																																																																						
①	②	③	④	⑤	⑥																																																																	
																																																																						
<table><tr><td>6</td><td>Outer Ferrule</td><td>Copper Alloy</td><td>Ni PLATED</td><td>4 PCS</td><td>4000PCS/R</td></tr><tr><td>5</td><td>Center Conductor</td><td>Copper Alloy</td><td>Gold PLATED</td><td>4 PCS</td><td>20KPCS/R</td></tr><tr><td>4</td><td>Dielectric</td><td>PA66</td><td></td><td>4 PCS</td><td></td></tr><tr><td>3</td><td>Outer Conductor</td><td>Copper Alloy</td><td>Ni PLATED</td><td>4 PCS</td><td></td></tr><tr><td>2</td><td>Housing</td><td>PBT</td><td></td><td>1 PC</td><td></td></tr><tr><td>1</td><td>Secondary Lock</td><td>PBT</td><td></td><td>2 PCS</td><td></td></tr><tr><td>NO.</td><td>SPEC.</td><td>MATERIAL</td><td>FINISH (Contact)</td><td>Q'TY</td><td>Note</td></tr></table>		6	Outer Ferrule	Copper Alloy	Ni PLATED	4 PCS	4000PCS/R	5	Center Conductor	Copper Alloy	Gold PLATED	4 PCS	20KPCS/R	4	Dielectric	PA66		4 PCS		3	Outer Conductor	Copper Alloy	Ni PLATED	4 PCS		2	Housing	PBT		1 PC		1	Secondary Lock	PBT		2 PCS		NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note	<table><tr><td>www.helloxkb.com</td><td>www.helloxkb.cn</td><td>www.xk-dg.cn</td></tr></table>		www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn	<table><tr><td colspan="2"></td><td>DESIGN</td><td>希文</td><td>VIEW: </td><td>MODEL TYPE: MINI FAKRA Female Connector for RG174</td></tr><tr><td>CHECKED</td><td></td><td colspan="2"></td><td>UNIT: mm/in</td><td>PART NO.: XMOTLF4S3-NJ06-X</td></tr><tr><td>APPROVED</td><td></td><td colspan="2"></td><td>SIZE: A4</td><td>DWG NO.: X-XMOTLF4S3-NJ06-X</td></tr></table>						DESIGN	希文	VIEW: 	MODEL TYPE: MINI FAKRA Female Connector for RG174	CHECKED				UNIT: mm/in	PART NO.: XMOTLF4S3-NJ06-X	APPROVED				SIZE: A4	DWG NO.: X-XMOTLF4S3-NJ06-X
6	Outer Ferrule	Copper Alloy	Ni PLATED	4 PCS	4000PCS/R																																																																	
5	Center Conductor	Copper Alloy	Gold PLATED	4 PCS	20KPCS/R																																																																	
4	Dielectric	PA66		4 PCS																																																																		
3	Outer Conductor	Copper Alloy	Ni PLATED	4 PCS																																																																		
2	Housing	PBT		1 PC																																																																		
1	Secondary Lock	PBT		2 PCS																																																																		
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note																																																																	
www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn																																																																				
		DESIGN	希文	VIEW: 	MODEL TYPE: MINI FAKRA Female Connector for RG174																																																																	
CHECKED				UNIT: mm/in	PART NO.: XMOTLF4S3-NJ06-X																																																																	
APPROVED				SIZE: A4	DWG NO.: X-XMOTLF4S3-NJ06-X																																																																	
1		2		3		4																																																																
				XKB INDUSTRIAL PRECISION CO.,LIMITED		SCALE	PAGE	REVISION																																																														
						N/A	1/2	A0																																																														

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.02	

Code List:

Colde							
	A	B	C	D	E	F	Z
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Water Blue/5021
PART NO.	XMOTLF4S3-NJ06-A	XMOTLF4S3-NJ06-B	XMOTLF4S3-NJ06-C	XMOTLF4S3-NJ06-D	XMOTLF4S3-NJ06-E	XMOTLF4S3-NJ06-F	XMOTLF4S3-NJ06-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: MINI FAKRA Female Connector for RG174
CHECKED		UNIT: mm/in	PART NO.: XMOTLF4S3-NJ06-X
APPROVED		SIZE: A4	DWG NO.: X-XMOTLF4S3-NJ06-X
			SCALE: N/A
			PAGE: 2/2
			REVISION: A0