Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
100V	1.05mΩ@10V	390A

合肥矽普半导体
Siliup Semiconductor Technology Co.Ltd
技术 品质 服务
www.siliup.com

Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

Applications

- PWM Application
- Hard switched and high frequency circuits
- Power Management

Package



TOLL

Circuit diagram



Marking



SP010N01GHTO : Product code
** : Week code

Order Information

Device	Package	Unit/Tape
SP010N01GHTO	TOLL	2000

Absolute maximum ratings (Ta=25℃ unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DS}	100	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current (Tc=25℃)	I_D	390	A
Continuous Drain Current (Tc=100℃)	I_D	260	A
Pulsed Drain Current	I_{DM}	1560	A
Single Pulse Avalanche Energy[1]	E_{AS}	2401	mJ
Power Dissipation (Tc=25℃)	P_D	435	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.29	℃/W
Storage Temperature Range	T_{STG}	-55 to 150	℃
Operating Junction Temperature Range	T_J	-55 to 150	℃

Electrical characteristics (Ta=25℃, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	VGS=0V , ID=250uA	100	110	-	V
Drain Cut-Off Current	I_{DSS}	VDS=80V , VGS=0V , TJ=25℃	-	-	1	μA
Gate Leakage Current	I_{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	$V_{GS(th)}$	VGS=VDS , ID =250uA	2	3	4	V
Drain-Source ON Resistance	$R_{DS(ON)}$	VGS=10V , ID=50A	-	1.05	1.3	mΩ
Dynamic Characteristics						
Input Capacitance	C_{iss}	VDS=50V , VGS=0V , f=1MHz	-	15756	-	pF
Output Capacitance	C_{oss}		-	1936	-	
Reverse Transfer Capacitance	C_{rss}		-	75	-	
Total Gate Charge	Q_g	VDS=50V , VGS=10V , ID=100A	-	268	-	nC
Gate-Source Charge	Q_{gs}		-	78	-	
Gate-Drain Charge	Q_{gd}		-	79	-	
Switching Characteristics						
Turn-On Delay Time	$t_{d(on)}$	VDD=50V, VGS=10V , RG=6Ω, ID=100A	-	83	-	nS
Rise Time	t_r		-	183	-	
Turn-Off Delay Time	$t_{d(off)}$		-	176	-	
Fall Time	t_f		-	67	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	V_{SD}	I_S = 1A, VGS = 0V	-	-	1.2	V
Maximum Body-Diode Continuous Current	I_S		-	-	390	A
Reverse Recovery Time	Trr	I_S=100A, di/dt=100A/us, TJ=25℃	-	90	-	nS
Reverse Recovery Charge	Qrr		-	209	-	nC

Note :

1. The test condition is VDD=50V,VGS=10V,L=0.5mH,RG=25Ω

Typical Characteristics



Output Characteristics



Transfer Characteristics



Capacitance Characteristics



Gate Charge



On-Resistance vs Gate to Source Voltage



Normalized On-Resistance



RDS(on) VS Drain Current



Forward characteristics of reverse diode



Normalized breakdown voltage



Normalized Threshold voltage



Current dissipation



Power dissipation



Maximum Transient Thermal Impedance



Safe Operation Area

TOLL Package Information



Symbol	Dimensions In Millimeters		
	Min.	Nom.	Max.
A	2.20	2.30	2.40
b	0.65	0.75	0.85
C		0.508 REF	
D	10.25	10.40	10.55
D1	2.85	3.00	3.15
E	9.75	9.90	10.05
E1	9.65	9.80	9.95
E2	8.95	9.10	9.25
E3	7.25	7.40	7.55
e		1.20 BSC	
F	1.05	1.20	1.35
H	11.55	11.70	11.85
H1	6.03	6.18	6.33
H2	6.85	7.00	7.15
H3		3.00 BSC	
L	1.55	1.70	1.85
L1	0.55	0.7	0.85
L2	0.45	0.6	0.75
M		0.08 REF.	
β	8°	10°	12°
K	4.25	4.40	4.55