

Data Sheet | Item Number: 216-264


Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

<https://www.wago.com/216-264>



Color: ■ black

Similar to illustration



Dimensions in mm

Connection data	
Cross-section metric	1.5 mm²
Strip length	14 ... 15 mm / 0.55 ... 0.59 inches
Cross-section AWG	16 AWG

Physical data	
Wall thickness plastic collar	0.25 mm
Total length	18 mm
Wall thickness crimp sleeve	0.15 mm
Crimp length (length of sleeve)	12 mm
Inner Diameter plastic collar	3.5 mm
Diameter crimp sleeve inside	1.7 mm

Mechanical data	
Plastic collar	Standard collar
Suitable	2002 to 2006 Series

Material data	
Color	black
Fire load	0.001 MJ
Weight	0.2 g


Commercial data	
Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 8.0	EC000005
PU (SPU)	1000 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918604291
Customs tariff number	85369010000





Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads


Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 216-264	

Documentation

Bid Text			
216-264	19.02.2019	xml 2.80 KB	
216-264	11.09.2017	doc 23.50 KB	

Installation Notes



A perfect gas-tight crimp – both electrical-ly and mechanically reliable