



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

Features

Product Type Features

Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Cable Entry Location	Side
----------------------	------

Mechanical Attachment

Thread Size	M25
Locking Device Location	Housing
Hood & Base Locking Device Type	Screwlock

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T2040242101-000  
DLX-024-M




TE Part # T3609250102-000  
DLX-25-M




TE Part # T1930240000-000  
H24BPR-AG

Also in the Series | HDC IP68 EMC




Connector Caps & Covers(4)




Rectangular Connector Hoods & Bases (444)




Customers Also Bought




TE Part #T2120100219-000  
ZGG-10DSTK,1-7,2-8,3-9,4-6,5-10




TE Part #1SNA195638R2300  
M4/6.4A.P




TE Part #T2106062201-000  
HWK6/6-012-F




TE Part #T2120100220-000  
ZGGP-H10BSK 1-7/2-8/3-9/4-6/5-10




TE Part #T0931003003-000  
CODING-PIN-M3




TE Part #640250-1  
01P SL156 HSG W/LCK RAMP NATL




TE Part #T1730060000-000  
H6B-TBF-T



TE Part #1-480711-9  
15P UMNL CAP HSG BLK



TE Part #T2020082201-000  
HD-008-F



TE Part #1473203-1  
025 CAP ASSY 16P P/BACK BRCKT

Documents

Product Drawings  
H24BPR-TSH-M25

English

CAD Files  
3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_T1910240125-000\_A.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_T1910240125-000\_A.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_T1910240125-000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English

Application Specification