



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: .32 – .82 mm²

Mating Tab Width: 6.35 mm [.25 in]

Mating Tab Thickness: .81 mm [.032 in]

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	19.05 mm[.75 in]
Compatible Insulation Diameter Range	1.52 – 2.54 mm[.06 – .1 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm ²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	12000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2376591-2 250 FASTON PCB TAB TPBR	 TE Part # 2150086-1 OCEAN-2.0-APPLICATOR-E-090F100O-REM	 TE Part # 171706-1 FASTON 250 INS POD NYLON NAT	 TE Part # 2376579-2 250 FASTON PCB TAB TPBR
 TE Part # 752856-1 DIES 90166-1	 TE Part # 336235-3 250 FASTON,REC.,24-17 AWG,PTBR	 TE Part # 2376595-2 250 FASTON PCB TAB TPBR	 TE Part # 737439-2 250 FASTON REC 22-18 AWG TPBR
 TE Part # 2150086-2 OCEAN-2.0-APPLICATOR-E-090F100O-REA	 TE Part # 7-2150086-7 OCEAN_2.0_SPARE_PART_KIT-090F100F	 TE Part # 2376582-2 250 FASTON PCB TAB TPBR	

Also in the Series | FASTON 250




Compression Connectors(4)



Crimp Terminal Housings(118)



Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(133)



Quick Disconnects(425)



Splices(4)

Customers Also Bought



TE Part #62814-2
250 FASTON FLAG REC 22-18 AWG TPBR



TE Part #T4112401041-000
M12,FEMALE,RA,B CODE,4P,PG7, GOLD




TE Part #2292802-3
AS16,PLUG BACKSHELL KIT,ST,12P, NC16



TE Part #61375-1
250 FASTON REC 18-14 AWG TPBR



TE Part #1-456404-1
CRIMPER WIRE .070 F




TE Part #505038-1
SHUR PLUG 180 CRIMP TAB 20-16 AWG BR



TE Part #42531-2
SHUR PLUG 180 RECEPTACLE 20-16 AWG TPBR



TE Part #1-456411-0
CRIMPER WIRE .140 F



TE Part #3-683452-3
ANVIL



TE Part #456134-1
CRIMPER, INSULATION "F"(.300")

Documents



Product Drawings

250 FASTON REC 22-18 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_42640-2_AV.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42640-2_AV.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42640-2_AV.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Engineering Report

English

Agency Approvals

UL Report

English