

74LVC1G125 Single Bus Buffer Gate

With 3-State Output

1. General Description

1.1 Description

This bus buffer gate is designed for 1.65V to 5.5V V_{CC} operation.

The 74LVC1G125 device is a single line driver with a 3-state output. The output is disabled when the output-enable ($\overline{OE}$) input is high.

The CMOS device has high output drive while maintaining low static power dissipation over a broad V_{CC} operating range.

1.2 Features

- Supports 5V V_{CC} operation
- Inputs accept voltages to 5.5V
- Provides down translation to V_{CC}

- Low power consumption, 10 μ A max I_{CC}
- ± 24 mA output drive at 3.3V
- I_{off} supports live insertion, partial-power-down mode, and back-drive protection

1.3 Device Information

PART NUMBER	PACKAGE
74LVC1G125	SOT23
	SC70
	SOT5X3
	DFN
	DSBGA

2. Connection Diagrams and Pin Description




Figure 2.1 Top View

PIN No.				NAME	I/O	FUNCTION
LT/CT/DT	BD/CD	ED	AG			
1	1	1	1	$\overline{OE}$	I	Input
2	2	2	2	A	I	Input
3	3	3	3	GND		Ground
4	4	4	4	Y	O	Output
5	6	5	5	VCC		Supply Voltage
--	5	--	--	NC		No Connected

3. System Diagram

3.1 Logic Diagram




Figure 3.1: 74LVC1G125 Logic Diagram

3.2 Function Table

Input		Output
$\overline{OE}$	A	Y
0	1	1
0	0	0
1	X	Z

X = don't care, 1=High State, 0=Low State,Z=High Impedance

4. Specifications

4.1 Absolute Maximum Ratings

Symbol	Parameter	MIN	MAX	Unit
V_{CC}	Supply Voltage	-0.5	6.5	V
V_I	Input Voltage Range	-0.5	6.5	V
V_O	Voltage Range(applied to any output in the high-impedance or power-off state) ⁽¹⁾	-0.5	6.5	V
	Voltage Range(applied to any output in the high or low state)	-0.5	$V_{CC} + 0.5$	V
I_O	Continuous Output Current		± 50	mA
T_J	Junction Temperature		125	°C
T_{OP}	Operating Temperature	0	70	°C

Absolute maximum ratings are those values beyond which the device could be permanently damaged. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under normal operating conditions.

- (1) The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.

4.2 Electrical Characteristics

4.2.1 DC Specifications

($T_a=25^{\circ}\text{C}$, voltages are referenced to GND (ground=0V), unless otherwise specified)

Symbol	Parameter	Test Condition	MIN	TYP	MAX	Unit
V_{IH}	High Level Input Voltage	$V_{CC}=1.65\text{V to }1.95\text{V}$	$0.65V_{CC}$	--	--	V
		$V_{CC}=2.3\text{V to }2.7\text{V}$	1.7	--	--	V
		$V_{CC}=3\text{V to }5.5\text{V}$	$0.7V_{CC}$	--	--	V
V_{IL}	Low Level Input Voltage	$V_{CC}=1.65\text{V to }1.95\text{V}$	--	--	$0.35V_{CC}$	V
		$V_{CC}=2.3\text{V to }2.7\text{V}$	--	--	0.7	V
		$V_{CC}=3\text{V to }3.6\text{V}$	--	--	0.8	V
		$V_{CC}=4.5\text{V to }5.5\text{V}$	--	--	$0.3V_{CC}$	V
I_{OH}	High Level Output Current	$V_{CC}=1.65\text{V}$	--	--	-4	mA
		$V_{CC}=2.3\text{V}$	--	--	-8	mA
		$V_{CC}=3\text{V}$	--	--	-16	mA
			--	--	-24	mA
		$V_{CC}=4.5\text{V}$	--	--	-32	mA
I_{OL}	Low Level Output Current	$V_{CC}=1.65\text{V}$	--	--	4	mA
		$V_{CC}=2.3\text{V}$	--	--	8	mA
		$V_{CC}=3\text{V}$	--	--	16	mA
			--	--	24	mA
		$V_{CC}=4.5\text{V}$	--	--	32	mA

Symbol	Parameter	Test Condition	MIN	TYP	MAX	Unit
V_{OH}	High Level Output Voltage	$V_{CC}=1.65V$ to $5.5V, I_{OH}=-100\mu A$	$V_{CC}-0.1$	--	--	V
		$V_{CC}=1.65V, I_O=-4mA$	--	1.49	--	V
		$V_{CC}=2.3V, I_O=-8mA$	--	2.2	--	V
		$V_{CC}=3V, I_O=-16mA$	--	2.85	--	V
		$V_{CC}=3V, I_O=-24mA$	--	2.75	--	V
		$V_{CC}=4.5V, I_O=-32mA$	--	4.25	--	V
V_{OL}	Low Level Output Voltage	$V_{CC}=1.65V$ to $5.5V, I_{OH}=100\mu A$	--	--	0.1	V
		$V_{CC}=1.65V, I_O=4mA$	--	0.05	--	V
		$V_{CC}=2.3V, I_O=8mA$	--	0.075	--	V
		$V_{CC}=3V, I_O=16mA$	--	0.15	--	V
		$V_{CC}=3V, I_O=24mA$	--	0.2	--	V
		$V_{CC}=4.5V, I_O=32mA$	--	0.25	--	V
I_I	A or OE Inputs Leakage Current	$V_{CC}=0$ to $5.5V, V_I=V_{CC}$ or GND	--	0	± 1	μA
I_{off}	Power Off Leakage Current	$V_{CC}=0V, V_I$ or $V_O=5.5V$	--	0	± 10	μA
I_{OZ}	3-State Output OFF-State Current	$V_{CC}=3.6V, V_O = 0$ to $5.5V$	--	0	10	μA
I_{CC}	Quiescent Supply Current	$V_{CC}=1.65V$ to $5.5V, V_I=V_{CC}$ or GND, $I_O=0$	--	0	10	μA
ΔI_{CC}	Additional Quiescent Supply Current Per Input Pin	$V_{CC}=3V$ to $5.5V$, one input at $V_{CC}-0.6V$, Other inputs at V_{CC} or GND	--	--	500	μA

5. Application Information




Figure 5.1: Application Schematic




6. Ordering Information

Orderable Device	Package Type	Pins	Packing	Package Qty
74LVC1G125LT05ARCQ	SOT23	5	Tape & Reel	3000
74LVC1G125CT05ARCQ	SC70	5	Tape & Reel	3000
74LVC1G125DT05ARDQ	SOT5x3	5	Tape & Reel	4000
74LVC1G125BD06AREQ	DFN(BD)	6	Tape & Reel	5000
74LVC1G125CD06AREQ	DFN(CD)	6	Tape & Reel	5000
74LVC1G125ED05ARCQ	DFN	5	Tape & Reel	3000
74LVC1G125AG05ARCQ	DSBGA	5	Tape & Reel	3000


7. Package Information

7.1 SOT23-5




Symbol	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	0.90	-	1.45	0.035	-	0.057
A1	-	-	0.15	-	-	0.006
A2	0.90	-	1.30	0.035	-	0.051
b	0.35	-	0.50	0.014	-	0.020
c	0.09	-	0.20	0.004	-	0.008
D	2.80	-	3.05	0.110	-	0.120
E	1.50	-	1.75	0.059	-	0.069
e	-	0.95	-	-	0.037	-
H	2.60	-	3.00	0.102	-	0.118
L	0.10	-	0.60	0.004	-	0.024
θ	0 degrees	-	10 degrees	-	-	-

7.2 SC70



Symbol	Dim in mm		
	MIN	TYP	MAX
A	0.90	1.00	1.10
A1	0.00	0.05	0.10
A2	0.90	0.95	1.00
b	0.15	0.25	0.35
C	0.10	0.12	0.15
D	1.80	2.00	2.20
E	2.15	2.25	2.35
E1	1.15	1.25	1.35
e	0.650TYP.		
e1	1.20	1.30	1.40
L	0.25	0.30	0.40
L2	0.15TYP.		
Y	0.00	0.05	0.10
θ	4°	8°	12°

7.3 SOT5X3








Figure 1: Mechanical drawing of the connector housing.

The drawing includes three views: a top view, a side view, and a front view.




Top View: Shows a rectangular housing with a "PIN 1 INDEX AREA" indicated by a dotted pattern. Dimensions include 1.05 and 0.95 for width and height.

Side View: Shows a "SEATING PLANE" and a dimension of 0.4 MAX.

Front View: Shows a symmetrical design with dimensions 0.7, 0.35, 0.1, 0.45, 0.35, 0.22, 0.12, and 0.05. A table of tolerances is provided at the bottom right.

Ø	0.07(M)	C	B	A
	0.05(M)	C		

7.6 DFN5



7.7 DSBGA

