




技术要求:

- 1 装配要求: SMA公头铆入杆套。
- 2 电气特性: 使用矢量网络分析仪100%测试,带线测试。
特性阻抗: 50Ω; 工作频率:2.4GHz-2.5GHz; 驻波比: ≤2.5。
- 3 尺寸检验: [*],FAI首件工艺检验项目; ◆,QIP重点检验项目; ★,CPK制程管制项目。
- 4 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污;镀层色泽光亮均匀,不得有氧化。
- 5 包装规范: 50PCS/袋。
- 6 环保要求: 制品及生产制程中所有使用到的物料皆须满足欧盟RoHS指令要求。

3	2SBWT4701	杆套: Ø13.79*L54.00,TPE-82956,白色	1
2	2LC15PM002	SMA主体: Ø10.00*L11.00,公头公针,主体镀镍,公针镀金	1
1	2C5R05800TP1	RG58芯线+绝缘: 内导体:纯铜线,1/0.9; 绝缘:PE,OD:2.85线	1
No.	PART NUMBER	PART NAME AND DESCRIPTION	Q'TY
BOM 物料清单			
GENERAL TOLERANCE: UNLESS OTHERWISE SPECIFIED LINEAR: 0.5 < L ≤ 6 ± 0.05 6 < L ≤ 30 ± 0.10 30 < L ≤ 120 ± 0.20 ANGULAR: 0 < L ≤ 10 ± 1°30' 10 < L ≤ 50 ± 1°00' 50 < L ≤ 120 ± 0°30'		FILE TYPE: 产品图	Dongguan HUANGJIE Communication Technology Co., Ltd. 东莞市皇捷通讯科技有限公司 TITLE: 射频天线组件 小蜜蜂天线,白色杆套,SMA公头公针, L=54mm (2.4GHz)
		DRA./DATE: S.He 23.09.05	
		CHE./DATE:	
		APP./DATE:	CODE: 3D4701WT00-001
		FILE FORM: HJ-QR-E-03 22.09.01	SIZE: A4
		UNIT: mm	PRO.: 3rd
		SCALE: 1:1	PAGE: 1/1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO HUANGJIE AND SHOULDN'T BE USED WITHOUT WRITTEN PERMISSION.

0 10 20