


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
AD	38		L	PLASTIC MATERIAL SUPPLIER CHANGED FOR HOUSING		07MAY2021	SB KJK

D

C

B

A




NOTES:

- TRUE POSITION TOLERANCE OF POST TIPS APPLIES WHEN HEADERS ARE HELD FLAT AGAINST PRINTED CIRCUIT BOARD.
-  .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL.
-  .000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
-  .000100-.000200 MATTE TIN OVER .000050 NICKEL.
-  OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SEE SHEET 2 FOR
ADDITIONAL LEAD FREE
PART NUMBERS

 OBSOLETE OBSOLETE		.125	.318	.184	.100	1	2	4- 87348 -3	
				4.840	4.000	40	40	4-	-2
				4.840	4.000	40	40	4-	-1
				3.984	3.900	39	40	4-	-0
				3.884	3.800	38	39	3-	-9
				3.784	3.700	37	38	3-	-8
				3.684	3.600	36	37	3-	-7
				3.584	3.500	35	36	3-	-6
				3.484	3.400	34	35	3-	-5
				3.384	3.300	33	34	3-	-4
				3.284	3.200	32	33	3-	-3
				3.184	3.100	31	32	3-	-2
				3.840	3.000	30	31	3-	-1
				2.984	2.900	29	30	3-	-0
				2.884	2.800	28	29	2-	-9
				2.784	2.700	27	28	2-	-8
				2.684	2.600	26	27	2-	-7
				2.584	2.500	25	26	2-	-6
				2.484	2.400	24	25	2-	-5
				2.384	2.300	23	24	2-	-4
				2.284	2.200	22	23	2-	-3
				2.184	2.100	21	22	2-	-2
				2.084	2.000	20	21	2-	-1
				1.984	1.900	19	20	2-	-0
				1.884	1.800	18	19	1-	-9
				1.784	1.700	17	18	1-	-8
				1.684	1.600	16	17	1-	-7
				1.584	1.500	15	16	1-	-6
				1.484	1.400	14	15	1-	-5
				1.384	1.300	13	14	1-	-4
				1.284	1.200	12	13	1-	-3
				1.184	1.100	11	12	1-	-2
				1.840	1.000	10	11	1-	-1
				.984	.900	9	10	1-	-0
				.884	.800	8	9		-9
				.784	.700	7	8		-8
				.684	.600	6	7		-7
				.584	.500	5	6		-6
				.484	.400	4	5		-5
				.384	.300	3	4		-4
				.284	.200	2	3		-3
				.184	.100	1	2		-2
		.125	.318	.084	0	0	1	87348 -1	
FINISH	E	D	C	B	A	NO OF POS	ASSEMBLY PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K HELM 6-89	 TE Connectivity				
DIMENSIONS: INCHES		CHK R. FEIDT 6-89					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APVD R. FEIDT 6-89	NAME				
		PRODUCT SPEC —	ASSEMBLY, MOD II, HEADER, SINGLE ROW, .100 C/L, VERTICAL, .025 SQ POSTS —				
		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL —	FINISH SEE TABLE	WEIGHT —	A2	00779	C-87348	—	
CUSTOMER DRAWING					SCALE 4:1	SHEET 1 of 2	REV L

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	38		—	SEE SHEET 1	—	—	—

	.125	.318	3.984	3.900	39	40	9- 87348 -0
			3.884	3.800	38	39	8-  -9
			3.784	3.700	37	38	8- -8
			3.684	3.600	36	37	8- -7
			3.584	3.500	35	36	8- -6
			3.484	3.400	34	35	8- -5
			3.384	3.300	33	34	8- -4
			3.284	3.200	32	33	8- -3
			3.184	3.100	31	32	8- -2
			3.840	3.000	30	31	8- -1
			2.984	2.900	29	30	8- -0
			2.884	2.800	28	29	7- -9
			2.784	2.700	27	28	7- -8
			2.684	2.600	26	27	7- -7
			2.584	2.500	25	26	7- -6
			2.484	2.400	24	25	7- -5
			2.384	2.300	23	24	7- -4
			2.284	2.200	22	23	7- -3
			2.184	2.100	21	22	7- -2
			2.084	2.000	20	21	7- -1
			1.984	1.900	19	20	7- -0
			1.884	1.800	18	19	6- -9
			1.784	1.700	17	18	6- -8
			1.684	1.600	16	17	6- -7
			1.584	1.500	15	16	6- -6
			1.484	1.400	14	15	6- -5
			1.384	1.300	13	14	6- -4
			1.284	1.200	12	13	6- -3
			1.184	1.100	11	12	6- -2
			1.840	1.000	10	11	6- -1
			.984	.900	9	10	6- -0
			.884	.800	8	9	5- -9
			.784	.700	7	8	5- -8
			.684	.600	6	7	5- -7
			.584	.500	5	6	5- -6
			.484	.400	4	5	5- -5
			.384	.300	3	4	5- -4
			.284	.200	2	3	5- -3
			.184	.100	1	2	5-  -2
	.125	.318	.084	0	0	1	5- 87348 -1
FINISH	E	D	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K HELM 6-89 CHK R. FEIDT 6-89 APVD R. FEIDT 6-89		 TE Connectivity			
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.005 4 PLC ± ANGLES ±				NAME ASSEMBLY, MOD II, HEADER, SINGLE ROW, .100 C/L, VERTICAL, .025 SQ POSTS -	
MATERIAL -		FINISH SEE TABLE		SIZE A2	GAGE CODE 00779		DRAWING NO C-87348
CUSTOMER DRAWING				SCALE 4:1	SHEET 2 of 2	REV L	