

Ceramic Singlelayer DC Disc Capacitors, 500 V_{DC} General Purpose



FEATURES

- High capacitance in small sizes
- Low losses
- Wide range of different lead styles
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS

- Bypassing, coupling and decoupling
- DC blocking
- Switching power supplies
- Lighting ballasts

DESIGN

The capacitors consist of a ceramic disc which is silver plated on both sides. Connection leads are made of tinned copper having diameters of 0.6 mm.

The capacitors may be supplied with straight or kinked leads having a lead spacing of 5.0 mm or 7.5 mm.

Coating is made of blue colored flame retardant epoxy resin in accordance with UL 94 V-0.

CAPACITANCE RANGE

10 pF to 10 nF

RATED VOLTAGE

500 V_{DC}

DIELECTRIC STRENGTH

1250 V_{DC}, 2 s Component test

INSULATION RESISTANCE AT 500 V_{DC}

≥ 5000 MΩ (60 s)

TOLERANCE ON CAPACITANCE

± 10 %, ± 20 %, - 20 % / + 50 %

DISSIPATION FACTOR

C < 100 pF: max. 3.0 % (1 MHz)

C ≥ 100 pF: max. 3.0 % (1 kHz)

QUICK REFERENCE DATA

DESCRIPTION	VALUE
Ceramic Class	2
Ceramic Dielectric	Y5T, Y5U
Voltage (V _{DC})	500
Min. Capacitance (pF)	10
Max. Capacitance (pF)	10 000
Mounting	Radial

OPERATING TEMPERATURE RANGE

-40 °C to +85 °C ⁽¹⁾

Note


⁽¹⁾ For explanation about the difference of operating temperature range and temperature characteristic of capacitance please see
www.vishay.com/doc?48299

TEMPERATURE CHARACTERISTICS

Y5T, Y5U

SECTIONAL SPECIFICATIONS

Climatic category (according to EN 60068-1):
40 / 085 / 21

DIMENSIONS in millimeters

ORDERING INFORMATION

CAPACITANCE (pF)	TOLERANCE (%)	BODY DIAMETER D _{max.} (mm)	BODY THICKNESS S _{max.} (mm)	LEAD SPACING ⁽¹⁾ F (mm) ± 1 mm	LEAD DIAMETER ⁽¹⁾ d (mm) ± 0.05 mm	WIDTH ⁽¹⁾ V (mm) ± 0.5 mm	ORDERING CODE
							MISSING DIGITS SEE ORDERING CODE BELOW
Y5T							
10	± 10, ± 20	6.0	3.0	5.0	0.6	1.6	HSZ100#AQ###KR
12							HSZ120#AQ###KR
15						1.5	HSZ150#AQ###KR
18						1.3	HSZ180#AQ###KR
22						1.1	HSZ220#AQ###KR
27						1.3	HSZ270#AQ###KR
33						1.4	HSZ330#AQ###KR
39							HSZ390#AQ###KR
47						1.2	HSZ470#AQ###KR
56							HSZ560#AQ###KR
68						1.4	HSZ680#AQ###KR
82							HSZ820#AQ###KR
100							HSZ101#AQ###KR
120				1.1	HSZ121#AQ###KR		
150					HSZ151#AQ###KR		
180				1.6	HSZ181#AQ###KR		
220					HSZ221#AQ###KR		
270				1.3	HSZ271#AQ###KR		
330					HSZ331#AQ###KR		
390				1.2	HSZ391#AQ###KR		
470					HSZ471#AQ###KR		
560					HSZ561#AQ###KR		
680					HSZ681#AQ###KR		
820		1.1		HSZ821#AQ###KR			
1000				HSZ102#AQ###KR			
1200		1.2		HSZ122#AQ###KR			
1500		1.1		HSZ152#AQ###KR			
1800		1.2		HSZ182#AQ###KR			
2200				HSZ222#AQ###KR			
2700				HSZ272#AQ###KR			
3300				HSZ332#AQ###KR			
3900		15.0				HSZ392#AQ###KR	
4700		1.1		HSZ472#AQ###KR			

ORDERING INFORMATION

CAPACITANCE (pF)	TOLERANCE (%)	BODY DIAMETER D _{max.} (mm)	BODY THICKNESS S _{max.} (mm)	LEAD SPACING ⁽¹⁾ F (mm) ± 1 mm	LEAD DIAMETER ⁽¹⁾ d (mm) ± 0.05 mm	WIDTH ⁽¹⁾ V (mm) ± 0.5 mm	ORDERING CODE
							MISSING DIGITS SEE ORDERING CODE BELOW
Y5U							
470	- 20 / + 50 ⁽²⁾	6.0	4.0	5.0	0.6	1.1	HSE471#AQ###KR
680						1.2	HSE681#AQ###KR
1000						1.4	HSE102#AQ###KR
1500		7.0		1.2		HSE152#AQ###KR	
2200						HSE222#AQ###KR	
3300		11.0		1.1		HSE332#AQ###KR	
4700						HSE472#AQ###KR	
6800						HSE682#AQ###KR	
8200		15.0		1.4		HSE822#AQ###KR	
10 000				1.2		HSE103#AQ###KR	

Notes



⁽¹⁾ Standard lead configuration, other lead spacing and diameter available on request

⁽²⁾ ± 20 % available on request

ORDERING CODE

#	7 th digit	Capacitance tolerance	± 10 % = K, ± 20 % = M, - 20 % / + 50 % = S				
###	10 th to 12 th digit	Lead configuration	See "General Information" www.vishay.com/doc?22001				
Example	HSE	103	S	AQ	CRY	K	R
	Series	Capacitance value	Tolerance code	Voltage code	Lead configuration	Internal code	RoHS compliant

MARKING

			
HSE 470 pF to 4.7 nF	HSE 6.8 nF to 10 nF	HSZ 10 pF to 3.9 nF	HSZ 4.7 nF

STORAGE

The capacitors must not be stored in a corrosive atmosphere, where sulphide or chloride gas, acid, alkali or salt are present. Exposure of the components to moisture, should be avoided. The solderability of the leads is not affected by storage of up to 24 months (temperature +10 °C to +35 °C, relative humidity up to 60 %). Class 2 ceramic dielectric capacitors are also subject to aging, see www.vishay.com/doc?22001.

SOLDERING

SOLDERING SPECIFICATIONS

Soldering test for capacitors with wire leads: (according to IEC 60068-2-20, solder bath method)		
	SOLDERABILITY	RESISTANCE TO SOLDERING HEAT
Soldering temperature	235 °C ± 5 °C	260 °C ± 5 °C
Soldering duration	2 s ± 0.5 s	10 s ± 1 s
Distance from component body	≥ 2 mm	≥ 5 mm



SOLDERING RECOMMENDATIONS

Soldering of the component should be achieved using a Sn60/40 type or a silver-bearing Sn62/36/2Ag type solder. Ceramic capacitors are very sensitive to rapid changes in temperature (thermal shock) therefore the solder heat resistance specification (see Soldering Specifications table) should not be exceeded. Subjecting the capacitor to excessive heating may result in thermal shocks that can crack the ceramic body. Similarly, excessive heating can cause the internal solder junction to melt.

CLEANING

The components should be cleaned immediately following the soldering operation with vapor degreasers.

SOLVENT RESISTANCE

The coating and marking of the capacitors are resistant to the following test method: IEC 60068-2-45 (method XA).

MOUNTING

If a defined product stop is required for mounting on a PCB, a mechanically formed product stop (kinked or inline wire) or a mounting tool should be used.

We do not recommend modifying the lead terminals, e.g. bending or cropping. This action could break the coating or crack the ceramic insert. If however, the lead must be modified in any way, we recommend support of the lead with a clamping fixture next to the coating.

OPERATING VOLTAGE

In case the voltage is applied to the circuit, starting as well as stopping, may generate irregular voltage for a transit period because of resonance or switching. Be sure to use a capacitor with a rated voltage range that includes these irregular voltages.

OPERATING TEMPERATURE AND SELF-GENERATED HEAT

Keep the surface temperature of a capacitor below the upper limit of its rated operating temperature range. Be sure to take into account the heat generated by the capacitor itself. When the capacitor is used in a high frequency, pulse, or similar application, it may have self-generated heat due to dielectric dissipation.

Temperature increase due to self-generated heating should not exceed 20 °C while operating at an atmosphere temperature of 25 °C.

When measuring, the surface temperature, make sure that the capacitor is not affected by radiant, conductive and convective heat by its surroundings. Excessive heat may lead to thermo-mechanical deterioration of the capacitor's characteristics and reliability.

RELATED DOCUMENTS

General Information

www.vishay.com/doc?22001



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.