



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: stsales@mail.taisaw.com Web: www.taisaw.com

Product Specifications Approval Sheet

Product Name: SAW Filter 790MHz SMD 3.0x3.0 mm (BW=40MHz)

TST Parts No.: TA2429A

Customer Parts No.: _____

Company: _____

Division: _____

Approved by : _____

Date: _____

Checked by: _____ Hong Pu Lin

Hong Pu Lin

Approval by: _____ Andy Yu

Andy Yu

Date: _____ 2019/06/05

1. Customer signed back is required before TST can proceed with sample build and receive orders.
2. Orders received without customer signed back will be regarded as agreement on the specifications.
3. Any specifications changes must be approved upon by both parties and a new revision of specifications shall be released to reflect the changes.

SAW Filter 790MHz

MODEL NO.: TA2429A

REV. NO.:2

A. MAXIMUM RATING:

1. Input Power Level: 20 dB_m(CW for 70000hrs at 25°C)
2. DC voltage: 5 V
3. Operating Temperature: -40°C to +105°C
4. Storage Temperature: -40°C to +105°C
5. Moisture Sensitivity Level: Level 1(**MSL1**)

 RoHS Compliant
 Lead free
 Lead-free soldering


Electrostatic Sensitive Device (ESD)

B. ELECTRICAL CHARACTERISTICS:


Item	Unit	min	type	Max
Center Frequency Fc	MHz		790	
Insertion Loss 770~810MHz (0°C to +50°C)	dB		2.7	3.5
Insertion Loss 770~810MHz (-40°C to +105°C)	dB		2.7	5
Return Loss 770~810MHz (0°C to +50°C)	dB	12	16	
Pass band 770~810MHz	MHz	40	52	
Attenuation (Reference level from 0dB)				
10~520	MHz	dB	45	52
520~700	MHz	dB	35	41
900~1240	MHz	dB	38	43
1240~1450	MHz	dB	32	38
Temperature Coefficient of Frequency	ppm/°C		-75 typ	

C. MEASUREMENT CIRCUIT:

HP Network analyzer



D. OUTLINE DRAWING:



△ : Year Code (2009->9, 2010->0, ..., 2018->8)


□ : Date Code (Follow the table from planner each year)

Date Code Table



WK01	WK02	WK03	WK04	WK05	WK06	WK07	WK08	WK09	WK10	WK11	WK12	WK13
A	B	C	D	E	F	G	H	I	J	K	L	M
WK14	WK15	WK16	WK17	WK18	WK19	WK20	WK21	WK22	WK23	WK24	WK25	WK26
N	O	P	Q	R	S	T	U	V	W	X	Y	Z
WK27	WK28	WK29	WK30	WK31	WK32	WK33	WK34	WK35	WK36	WK37	WK38	WK39
a	b	c	d	e	f	g	h	i	j	k	l	m
WK40	WK41	WK42	WK43	WK44	WK45	WK46	WK47	WK48	WK49	WK50	WK51	WK52
n	o	p	q	r	s	t	u	v	w	x	y	z



E. PCB Footprint:

4



F. Frequency Characteristics:







G. PACKING: (Ref. WI-75M03)

1. REEL DIMENSION

(Please refer to FR-75D10 for packing quantity)



2. TAPE DIMENSION



H. Recommended Reflow Profile:

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds min.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C +0/-5°C peak (20~40sec).
4. Time: 2 times.

