

Ultra-Low Noise Microphone with Differential Output

GENERAL DESCRIPTION

The ICS-40730 is an ultra-low noise, differential analog output, bottom-ported MEMS microphone. The ICS-40730 includes a MEMS microphone element, an impedance converter, a differential output amplifier and an enhanced RF package. The ICS-40730's 74 dB SNR and ±2 dB sensitivity tolerance make it an excellent choice for microphone arrays and far field voice control applications.

The ICS-40730 has a linear response up to 123 dB SPL with a differential output sensitivity specification of -32 dBV. It can be used in a single-ended mode with -38 dBV sensitivity and the same high SNR.

The ICS-40730 is available in a 4.72 mm \times 3.76 mm \times 3.50 mm surface-mount package.


APPLICATIONS

- Smart Home Devices
- Smartphones
- Teleconferencing Systems
- Security and Surveillance
- Microphone Arrays
- Voice Control and Activation

FEATURES

- Ultra-High 74 dBA SNR
- –32 dBV Differential Sensitivity, –38 dBV Single-Ended Sensitivity
- ±2 dB Sensitivity Tolerance
- 4.72 × 3.76 × 3.5 mm Surface-Mount Package
- Non-Inverted Signal Output
- Extended Frequency Response from 20 Hz to 20 kHz
- Enhanced RF Performance
- 285 μA Current Consumption
- 123 dB SPL Acoustic Overload Point
- −77 dBV PSR
- Compatible with Sn/Pb and Pb-Free Solder Processes
- RoHS/WEEE Compliant

FUNCTIONAL BLOCK DIAGRAM



ORDERING INFORMATION

PART	TEMP RANGE	PACKAGING
ICS-40730	-40°C to +85°C	13" Tape and Reel
EV_ICS-40730-FX	_	_



TABLE OF CONTENTS

General Description	1
Applications	1
Features	1
Functional Block Diagram	1
Ordering Information	1
Table of Contents	2
Specifications	3
Table 1. Electrical Characteristics	3
Absolute Maximum Ratings	4
Table 2. Absolute Maximum Ratings	4
ESD Caution	4
Soldering Profile	5
Table 3. Recommended Soldering Profile*	5
Pin Configurations And Function Descriptions	6
Table 4. Pin Function Descriptions	6
Typical Performance Characteristics	7
Theory Of Operation	8
Balanced Output	8
Single-Ended Operation	8
Applications Information	9
Codec Connection	9
Supporting Documents	10
Evaluation Board User Guide	10
Application Notes	10
PCB Design And Land Pattern Layout	11
PCB Material And Thickness	11
Handling Instructions	12
Pick And Place Equipment	12
Reflow Solder	12
Board Wash	12
Outline Dimensions	13
Ordering Guide	13
Revision History	
Compliance Declaration Disclaimer	15



SPECIFICATIONS

TABLE 1. ELECTRICAL CHARACTERISTICS

 $T_A = 25$ °C, $V_{DD} = 1.5$ to 3.63 V, unless otherwise noted. Typical specifications are not guaranteed.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES
PERFORMANCE				•		
Directionality			Omni			
Consistings	1 kHz, 94 dB SPL, differential -		-32	-30	dBV	
Sensitivity	1 kHz, 94 dB SPL, single-ended	-40	-38	-36	dBV	
	20 Hz to 20 kHz, A-weighted,		74		dBA	
Signal-to-Noise Ratio (SNR)	differential		/4		UDA	
Signal-to-Noise Natio (SiVIV)	20 Hz to 20 kHz, A-weighted,		74		dBA	
	single-ended	/4			UDA	
Equivalent Input Noise (EIN)	20 Hz to 20 kHz, A-weighted		20		dBA SPL	
Dynamic Range	Derived from EIN and maximum		103		dB	
Dynamic Range	acoustic input		103		ив	
Frequency Response	Low frequency -3 dB point		20		Hz	
rrequericy Response	High frequency -3 dB point		>20		kHz	
Total Harmonic Distortion (THD)	105 dB SPL			0.6	%	
	217 Hz, 100 mVp-p square wave				dBV	
Power-Supply Rejection (PSR)	superimposed on $V_{DD} = 1.8 V$,		-77			
	A-weighted					
Downer Complet Delegation Detic (DCDD)	1 kHz, 100 mV p-p sine wave		4.5		40	
Power Supply Rejection Ratio (PSRR)	superimposed on V _{DD} = 1.8 V	1 -/15			dB	
Acoustic Overload Point	10% THD		123		dB SPL	
POWER SUPPLY						
Supply Voltage (V _{DD})		1.5		3.63	V	
Supply Current (I _s)						
	V _{DD} = 1.8 V		285	350	μΑ	
	V _{DD} = 3.3 V			375	μΑ	
OUTPUT CHARACTERISTICS		•	•			
Output Impedance	Differential		430		Ω	
	Cinale Foded OUTPUT:		100			
	Single-Ended, OUTPUT+		180		Ω	
	Single-Ended, OUTPUT-		250		Ω	
Output DC Offset	OUTPUT+		0.72		V	
	OUTPUT-		0.66		V	
Maximum Output Voltage	Differential, 123 dB SPL input	Differential, 123 dB SPL input			V rms	
	Single-Ended, 123 dB SPL input		0.40		V rms	
Noise Floor	20 Hz to 20 kHz, A-weighted, rms		-106		dBV	



ABSOLUTE MAXIMUM RATINGS

Stress above those listed as Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these conditions is not implied. Exposure to the absolute maximum ratings conditions for extended periods may affect device reliability.

TABLE 2. ABSOLUTE MAXIMUM RATINGS

PARAMETER	RATING
Supply Voltage (V _{DD})	-0.3 V to +3.63 V
Sound Pressure Level	160 dB
Mechanical Shock	10,000 g
Vibration	Per MIL-STD-883 Method 2007, Test Condition B
Temperature Range	
Biased	-40°C to +85°C
Storage	-55°C to +150°C

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

SOLDERING PROFILE





Figure 1. Recommended Soldering Profile Limits

TABLE 3. RECOMMENDED SOLDERING PROFILE*

PROFILE FEATURE		Sn63/Pb37	Pb-Free	
Average Ramp Rate (T _L to T _P)		1.25°C/sec max	1.25°C/sec max	
Preheat	Minimum Temperature (T _{SMIN})	100°C	100°C	
	Maximum Temperature (T _{SMAX})	150°C	200°C	
	Time (T_{SMIN} to T_{SMAX}), t_S	60 sec to 75 sec	60 sec to 75 sec	
Ramp-Up Rate (T _{SMAX} to T _L)		1.25°C/sec	1.25°C/sec	
Time Maintained Above Liquidous (t _L)		45 sec to 75 sec	~50 sec	
Liquidous Temperature (T _L)		183°C	217°C	
Peak Temperature (T _P)		215°C +3°C/-3°C	260°C +0°C/-5°C	
Time Within +5°C of Actual Peak Temperature (t _P)		20 sec to 30 sec	20 sec to 30 sec	
Ramp-Down Rate		3°C/sec max	3°C/sec max	
Time +25°C (t _{25°C}) to Peak Temperature		5 min max	5 min max	

^{*}Note: The reflow profile in Table 3 is recommended for board manufacturing with InvenSense MEMS microphones. All microphones are also compatible with the J-STD-020 profile

PIN CONFIGURATIONS AND FUNCTION DESCRIPTIONS



TOP VIEW (TERMINAL SIDE DOWN) Not to Scale

Figure 2. Pin Configuration

TABLE 4. PIN FUNCTION DESCRIPTIONS

PIN	NAME	FUNCTION	
1	VDD	Power Supply	
2	OUTPUT+	Noninverting analog output signal relative to the acoustic input	
3	OUTPUT-	Inverting analog output signal relative to the acoustic input	
4	GND	Ground	

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 3. Typical Frequency Response (Measured)




Figure 4. THD + N vs. Input Level




Figure 5. Power-Supply Rejection Ratio (PSRR) vs. Frequency




Figure 6. Linearity



THEORY OF OPERATION

BALANCED OUTPUT

The ICS-40730 has a balanced differential output with 430 Ω output impedance. This configuration is compatible with a fully-differential codec input and provides the benefits of a balanced signal between the microphone and codec. A balanced analog audio signal provides rejection of common-mode noise that is present on both the positive and negative signals.

SINGLE-ENDED OPERATION

The ICS-40730 can be used as a single-ended microphone by using the signal from only one of the two output pins. In this configuration, the sensitivity will be 6 dB lower than the differential output, but with the same high SNR performance. Pin OUTPUT+ will output the non-inverted signal, relative to the acoustic input, while the OUTPUT- pin will output an inverted signal. The unused output pin should be left disconnected when the mic is used in single-ended mode; do not connect the unused pin to ground.

APPLICATIONS INFORMATION

CODEC CONNECTION

The ICS-40730 output can be connected to a dedicated codec microphone input (see Figure 7) or to a high input impedance gain stage. A $0.1~\mu\text{F}$ ceramic capacitor placed close to the ICS-40730 supply pin is used for testing and is recommended to adequately decouple the microphone from noise on the power supply. DC blocking capacitors are required at the outputs of the microphone. These capacitors create a high-pass filter with a corner frequency at

$$f_C = 1/(2\pi \times C \times R)$$

where *R* is the input impedance of the codec.

A minimum value of 2.2 μ F is recommended in Figure 7 because the input impedance of some codecs can be as low as 2 $k\Omega$ at their highest PGA gain setting, which results in a high-pass filter corner frequency at 37 Hz.




Figure 7. ICS-40730 Connected to a Differential-Input Codec



SUPPORTING DOCUMENTS

For additional information, see the following documents.

EVALUATION BOARD USER GUIDE

AN-000012, Differential Analog Output MEMS Microphone Flex Evaluation Board

APPLICATION NOTES

AN-100, MEMS Microphone Handling and Assembly Guide

AN-1003, Recommendations for Mounting and Connecting the InvenSense Bottom-Ported MEMS Microphones

AN-1112, Microphone Specifications Explained

AN-1124, Recommendations for Sealing InvenSense Bottom-Port MEMS Microphones from Dust and Liquid Ingress

AN-1140, Microphone Array Beamforming

AN-1165, Op Amps for Microphone Preamp Circuits

AN-1181, Using a MEMS Microphone in a 2-Wire Microphone Circuit

PCB DESIGN AND LAND PATTERN LAYOUT

Lay out the PCB land pattern for the ICS-40730 at a 1:1 ratio to the solder pads on the microphone package (see Figure 8.) Take care to avoid applying solder paste to the sound hole in the PCB. Figure 9 shows a suggested solder paste stencil pattern layout. The response of the ICS-40730 is not affected by the PCB hole size, as long as the hole is not smaller than the sound port of the microphone (1.5 mm, or 0.059 inch, in diameter). A 2 mm (0.080 inch) diameter for the hole is recommended.

Align the hole in the microphone package with the hole in the PCB. The exact degree of the alignment does not affect the performance of the microphone as long as the holes are not partially or completely blocked.




Figure 8. Suggested PCB Land Pattern Layout




Figure 9. Suggested Solder Paste Stencil Pattern Layout

PCB MATERIAL AND THICKNESS

The performance of the ICS-40730 is not affected by PCB thickness. The ICS-40730 can be mounted on either a rigid or flexible PCB. A flexible PCB with the microphone can be attached directly to the device housing with an adhesive layer. This mounting method offers a reliable seal around the sound port while providing the shortest acoustic path for good sound quality.



HANDLING INSTRUCTIONS

The ICS-40730 has a large sound hole, allowing for exposure of the diaphragm to the outside world. Care should be taken to any prevent any particulate or objects from contaminating or impacting the diaphragm.

PICK AND PLACE EQUIPMENT

The MEMS microphone can be handled using standard pick-and-place and chip shooting equipment. Take care to avoid damage to the MEMS microphone structure as follows:

- Use a standard pickup tool to handle the microphone. Because the microphone hole is on the bottom of the package, the pickup tool can make contact with any part of the lid surface.
- Do not pick up the microphone with a vacuum tool that makes contact with the bottom side of the microphone.
- Do not pull air out of or blow air into the microphone port.
- Do not use excessive force (>1 kg) to place the microphone on the PCB.

REFLOW SOLDER

For best results, the soldering profile must be in accordance with the recommendations of the manufacturer of the solder paste used to attach the MEMS microphone to the PCB. It is recommended that the solder reflow profile not exceed the limit conditions specified in Figure 1 and Table 3.

BOARD WASH

When washing the PCB, ensure that water does not make contact with the microphone port. Do not use blow-off procedures or ultrasonic cleaning.

OUTLINE DIMENSIONS




Figure 10. 4-Terminal Chip Array Small Outline No Lead Cavity 4.72 mm × 3.76 mm × 3.5 mm **Dimensions shown in millimeters**




Figure 11. Package Marking Specification (Top View)

ORDERING GUIDE

PART	TEMP RANGE	PACKAGE	QUANTITY	PACKAGING
ICS-40730	-40°C to +85°C	4-Terminal LGA_CAV	2,000	13" Tape and Reel
EV_ICS-40730-FX		Flex Evaluation Board		

NOTE:
1. ALL DIMENSION ARE IN MILLIMETER.
2. GENERAL TOLERANCE: ±0.10mm UNLESS SPECIFIED

REVISION HISTORY

REVISION DATE	REVISION	DESCRIPTION
07/06/2017	1.0	Initial Release
05/19/2020 1.1		Corrected typos and updated pin polarity; updated Figure 2, Table 4, and Figure 10 caption



COMPLIANCE DECLARATION DISCLAIMER

InvenSense believes the environmental and other compliance information given in this document to be correct but cannot guarantee accuracy or completeness. Conformity documents substantiating the specifications and component characteristics are on file. InvenSense subcontracts manufacturing, and the information contained herein is based on data received from vendors and suppliers, which has not been validated by InvenSense.

This information furnished by InvenSense, Inc. ("InvenSense") is believed to be accurate and reliable. However, no responsibility is assumed by InvenSense for its use, or for any infringements of patents or other rights of third parties that may result from its use. Specifications are subject to change without notice. InvenSense reserves the right to make changes to this product, including its circuits and software, in order to improve its design and/or performance, without prior notice. InvenSense makes no warranties, neither expressed nor implied, regarding the information and specifications contained in this document. InvenSense assumes no responsibility for any claims or damages arising from information contained in this document, or from the use of products and services detailed therein. This includes, but is not limited to, claims or damages based on the infringement of patents, copyrights, mask work and/or other intellectual property rights.

Certain intellectual property owned by InvenSense and described in this document is patent protected. No license is granted by implication or otherwise under any patent or patent rights of InvenSense. This publication supersedes and replaces all information previously supplied. Trademarks that are registered trademarks are the property of their respective companies. InvenSense sensors should not be used or sold in the development, storage, production or utilization of any conventional or mass-destructive weapons or for any other weapons or life threatening applications, as well as in any other life critical applications such as medical equipment, transportation, aerospace and nuclear instruments, undersea equipment, power plant equipment, disaster prevention and crime prevention equipment.

©2020 InvenSense. All rights reserved. InvenSense, MotionTracking, MotionProcessing, MotionProcessor, MotionFusion, MotionApps, DMP, AAR, and the InvenSense logo are trademarks of InvenSense, Inc. The InvenSense logo is a trademark of InvenSense Corporation. Other company and product names may be trademarks of the respective companies with which they are associated.



©2020 InvenSense. All rights reserved.