



布电线 BUILDING WIRES

RVB Z(A,B,C,D)-RVB 300/300V

标称截面 Nominal section (mm ²)	外径上限 Toplimit of overall diameter (mm)	20℃最大直流电阻 Maximum DC resistance (20℃) (Ω/km)	70℃最小绝缘电阻 Minimum insulation resistance (70℃) (MΩ·km)	载流量推荐值 Recommended value of carrying capacity (A)	电缆参考重量 Reference weight (kg/km)
2×0.3	2.3×4.3	69.2	0.016	7.4	12.6
2×0.4	2.5×4.6	48.2	0.014	9.0	16.0
2×0.5	3.0×5.8	39.0	0.016	10.0	22.0
2×0.75	3.2×6.4	26.0	0.014	13.0	29.0
2×1.0	3.3×6.6	19.5	0.012	16.0	35.0

RV-105℃ (60227 IEC08 型) Z(A,B,C,D)-RV-105℃ 300/300V 450/750V

标称截面 Nominal section (mm ²)	外径上限 Toplimit of overall diameter (mm)	20℃最大直流电阻 Maximum DC resistance (20℃) (Ω/km)	70℃最小绝缘电阻 Minimum insulation resistance (70℃) (MΩ·km)	载流量推荐值 Recommended value of carrying capacity (A)	电缆参考重量 Reference weight (kg/km)
0.5	2.5	39.0	0.013	13.3	10.0
0.75	2.7	26.0	0.012	17.0	13.3
1.0	2.8	19.5	0.010	20.0	16.0
1.5	3.4	13.3	0.009	25.4	21.6
2.5	4.1	7.98	0.009	34.5	34.0
4	4.8	4.95	0.008	44.5	50.0
6	5.3	3.30	0.006	58.3	75.0

RVS Z(A,B,C,D)-RVS 300/300V

标称截面 Nominal section (mm ²)	外径上限 Toplimit of overall diameter (mm)	20℃最大直流电阻 Maximum DC resistance (20℃) (Ω/km)	70℃最小绝缘电阻 Minimum insulation resistance (70℃) (MΩ·km)	载流量推荐值 Recommended value of carrying capacity (A)	电缆参考重量 Reference weight (kg/km)
2×0.5	6.0	39.0	0.013	13.3	24.0
2×0.75	6.2	26.0	0.011	17.0	31.0
2×1.0	6.6	19.5	0.010	20.0	36.5
2×1.5	7.2	13.3	0.010	25.4	47.2
2×2.5	8.2	7.98	0.009	34.5	66.8
2×4	9.2	4.95	0.007	44.5	97.3
2×6	10.6	3.30	0.006	58.3	138.9