

SIGN	DATE	DESCRIPTION	APPROVER
△	12/02'08	With flange screw changed from“-“slot type to“+/-“slot type	Jacke
△	2010.10.28	Add UL standard	Jacke
△	2010.10.28	The design is changed	Jacke
△	2010.10.28	The design is changed	Jacke
△	2012.07.16	Change the material of contact from Brass to Copper	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- ItemⒶ Terminal (housing):Thermoplastic (UL94V-0)
- ItemⒷ Terminal (Cover):Thermoplastic (UL94V-0)
- ItemⒸ Terminal screw:Steel Zinc plating “-“ slot type
- ItemⒹ Clamp:Brass(CuZn) nickel plating
- △ ● ItemⒺ Male Contact Pin: Copper, Tin plated
- △ ● ItemⒻ Flange Screw: Steel Zine plating “+/-“ slot type

Electrical




- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 4 Lb-In
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40℃ to +115℃
- △ ● Safety Approval: 
- Critical dimension: ▽

V8 xx 01 x 2 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
16 16 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

G: RoHS complian(lead<4%)
In copper Alloy
0000: “@” Logo (Standard)
000A: “ANYTEK” Mark
Any special item by
customer request.
please contact sales
department.



N = Number of poles

DIMENSION

Dim A	(N-1)X7.62+7.52
Dim B	(N-1)X7.62

Poles	Tolerance
2p-4p	±0.15
5p-8p	±0.25
9p-12p	±0.30
13p-16p	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V8 7.62 Series with flange screw type				
PART NO.	V8xx01x2xxxxG			DWG NO.	8V80503	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Chen Bo 2012.07.16	Chen Bo 2012.07.16		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: E	X.XX ±0.10
						X° ±1°