









Specifications :

- Voltage rating: 350V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -55°C~+105°C
- Insulation resistance: $\geq 100M\Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing : $\leq 40m\Omega$

X1511 W V S-XX L HF-LP SW
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : V-Straight 180°
- ④ Welding Way:S-SMT
- ⑤ Row No.-Pin No.: XX-02P~15P
- ⑥ Plug the Pin & Special NO.:L-With Lock
- ⑦ Plug the Pin & Special NO.:HF-Halogen free
- ⑧ Material : 9T-PA9T;46-PA46;LP-LCP 94V-0
- ⑨ Planting Category:SW-Matte Tin Plating

Poles	Dimensions(mm)		
	A	B	C
02	1.50	4.30	3.70
03	3.00	5.80	5.20
04	4.50	7.30	6.70
05	6.00	8.80	8.20
06	7.50	10.30	9.70
07	9.00	11.80	11.20
08	10.50	13.30	12.70
09	12.00	14.80	14.20
10	13.50	16.30	15.70
11	15.00	17.80	17.20
12	16.50	19.30	18.70
13	18.00	20.80	20.20
14	19.50	22.30	21.70
15	21.00	23.80	23.20

X1511WVS-XXLHF-LPSW	LCP UL 94V-0 Halogen Free	Brass	Matte Tin Plating	X1511H
PART NO	Material	Material(Pin&Solder Tail)	Finish(Pin)	Suitable XKB Terminal

DSND		DATE		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connectors
DWN		DATE		VIEW:	PART NO.: X1511WVS-XXLHF-XXSW
CHKD		DATE		UNIT: mm/in	DWG NO.: X-X1511WVS-XXLHF-XXSW
APPD		DATE		SIZE: A4	WEIGHT 1.0g
XKB INDUSTRIAL PRECISION CO.,LIMITED					SHEET 1/1
					REVISION A0

广东星坤科技股份有限公司

Δx		日期
Δx		
Δx		
MARK		

文件工程章

REVISIONS	DATE	REVISED	APPROVED
UNSPECIFIED TOLERANCES			

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn