


PIN RECEPTACLES

FOR 0,56 - 0,86 DIAMETER PINS AND 0,64 SQUARE PINS

9808

9808-0-15-XX-16-XX-04-0


Press-fit in 1,70 mounting hole



9101

9101-0-15-XX-16-XX-10-0


Press-fit in 1,70 mounting hole



5650

5650-0-19-XX-16-XX-10-0


Press-fit in 1,70 mounting hole



8679

8679-0-15-XX-16-XX-10-0


Solder mount in 1,80 min. mounting hole



8827

8827-0-15-XX-16-XX-04-0


Press-fit in 1,55 mounting hole



6021

6021-0-15-XX-16-XX-10-0


Solder mount in 1,57 min. mounting hole



1873

1873-0-15-XX-16-XX-04-0


Press-fit in 1,68 mounting hole



5070

5070-0-18-XX-16-XX-10-0

Press-fit in 1,55 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - 16 - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76µm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#16 CONTACT (DATA ON PAGE 256)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com