





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F1	REVISED PER ECO-11-004835	11MAR11	RK	HMR




RECOMMENDED PC BOARD LAYOUT (VIEWED FROM CONNECTOR SIDE)



SECTION U-U

TIPS	OBSOLETE	BLUE	78.74 [3.100]	31	80.77 [3.180]	86.26 [3.396]	88.90 [3.500]	64	3-1761609-7
			73.66 [2.900]	29	75.69 [2.980]	81.18 [3.196]	83.82 [3.300]	60	3-1761609-6
			60.96 [2.400]	24	62.99 [2.480]	68.48 [2.696]	71.12 [2.800]	50	3-1761609-5
			48.26 [1.900]	19	50.29 [1.980]	55.78 [2.196]	58.42 [2.300]	40	3-1761609-3
			40.64 [1.600]	16	42.67 [1.680]	48.16 [1.896]	50.80 [2.000]	34	3-1761609-1
			35.56 [1.400]	14	37.59 [1.480]	43.08 [1.696]	45.72 [1.800]	30	3-1761609-0
			30.48 [1.200]	12	32.51 [1.280]	38.00 [1.496]	40.64 [1.600]	26	2-1761609-9
			27.94 [1.100]	11	29.97 [1.180]	35.46 [1.396]	38.10 [1.500]	24	2-1761609-8
			22.86 [.900]	9	24.89 [.980]	30.38 [1.196]	33.02 [1.300]	20	2-1761609-7
			17.78 [.700]	7	19.81 [.780]	25.30 [.996]	27.94 [1.100]	16	2-1761609-6
			15.24 [.600]	6	17.27 [.680]	22.76 [.896]	25.40 [1.000]	14	2-1761609-5
			12.70 [.500]	5	14.73 [.580]	20.22 [.796]	22.86 [.900]	12	2-1761609-4
			10.16 [.400]	4	12.19 [.480]	17.68 [.696]	20.32 [.800]	10	2-1761609-3
			5.08 [.200]	2	7.11 [.280]	12.60 [.496]	15.24 [.600]	6	2-1761609-1
			OBSOLETE	BLACK	73.66 [2.900]	29	75.69 [2.980]	81.18 [3.196]	83.82 [3.300]
60.96 [2.400]	24	62.99 [2.480]			68.48 [2.696]	71.12 [2.800]	50	1-1761609-5	
48.26 [1.900]	19	50.29 [1.980]			55.78 [2.196]	58.42 [2.300]	40	1-1761609-3	
40.64 [1.600]	16	42.67 [1.680]			48.16 [1.896]	50.80 [2.000]	34	1-1761609-1	
30.48 [1.200]	12	32.51 [1.280]			38.00 [1.496]	40.64 [1.600]	26	1761609-9	
22.86 [.900]	9	24.89 [.980]			30.38 [1.196]	33.02 [1.300]	20	1761609-7	
17.78 [.700]	7	19.81 [.780]			25.30 [.996]	27.94 [1.100]	16	1761609-6	
15.24 [.600]	6	17.27 [.680]			22.76 [.896]	25.40 [1.000]	14	1761609-5	
10.16 [.400]	4	12.19 [.480]			17.68 [.696]	20.32 [.800]	10	1761609-3	
HOUSING COLOR	E	D			C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30JUN05 B.CRISAMORE/DTI CHK 30JUN05 S.BOLASH APVD 30JUN05 M.WALMSLEY PRODUCT SPEC — APPLICATION SPEC —		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.13[.005] 4 PLC ± — ANGLES ± —		NAME HEADER ASSEMBLY, SHORT EJECT LATCH, RIGHT ANGLE, LOW PROFILE, IDC —	
		WEIGHT —		SIZE CAGE CODE DRAWING NO A1 00779 C-1761609	
MATERIAL 		FINISH 		RESTRICTED TO —	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1 REV F1	