


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C200383	2020-03-28	Peng	△BXI


SAFI6B-XXG03



01:MPQ(2000PCS)/REEL
02:LOOSE PIECE 500PCS
03:LOOSE PIECE 100PCS



SECTION A-A



SECTION B-B

Note:

* Material

Contact Body: Copper Alloy

Outer Spring: Stainless steel

* Contact Finish: 3u"Min Gold Plating


* Current Rating: 10A Max

* Termination Type: Crimping

* Wire Range: 18AWG~16AWG

* Salt Spray Test 48H

* This drawing is supplied for information only design features specifications and performance data



UNIT:mm



TOLERANCE

±0.5

TITLE

10A FEMALE CLAW PIN TERMINAL

SCALE 4:1

SIZE A4

SHEET 1 OF 1

REV. B

WC-REV. A.2

QC:Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

SAFI6B-XXG03

CUSTOMER

ALTW

DRAWN BY

Jinhai

CHECKED BY

Rensong

APPROVED BY

Jerry

DATE

2015-08-12

DATE

2015-08-12

DATE

2015-08-12