







PCB LAYOUT

2P to 6P with wedge,
above 7P without wedge.



N = Number of poles
 Dim A=(N-1)x3.81+2.8
 Dim B=(N-1)x3.81
 Dim C=(N-1)x3.5+3.7
 Dim D=(N-1)x3.81

	Dim A	Dim B	Dim C	Dim D
2-5p	±0.10	±0.10	±0.10	±0.10
6-10p	±0.15	±0.15	±0.15	±0.15
11-15p	±0.20	±0.20	±0.20	±0.20
16-20p	±0.25	±0.25	±0.25	±0.25
21-24p	±0.30	±0.30	±0.30	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.01.12	Add cULus standard	Jacke
△	2013.08.10	change the dimension from 0.93 to 1.07	Chen Bo
△	2013.08.10	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

Item a Terminal body:Thermoplastic (UL94V-0)

Item b Female contact:PhBz(CuSn),Tin plated

Electrical

- Voltage rating: 300V AC
- Current rating: 8A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ∇

V7 xx 3 1 x 0 xxxx G

No. OF POLES

02 2 CONTACTS

03 3 CONTACTS

... 24 24 CONTACTS

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@ " Logo (Standard)

000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 3.81 Series Vertical			
PART NO.	V7xx31x0xxxxG			DWG NO.	8V70102
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Chen Bo 08/10`13	Chen Bo 08/08`13	Tolerance	
				UNIT: mm	X. ±0.5
				SCALE: NONE	X.X ±0.3
				SHEET: 01/01	X.XX ±0.1
				REV.: D	X° ±1°