




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	9	RIBS ADDED AT BOTH ENDS	29MAR2019	HSR	PS
	10	RIB ADDED ON LATCH	17JUL2019	AY	PS
	11	OVERALL LENGTH UPDATED	12SEP2019	AY	PS
	12	REMOVED NOTE 5	19SEP2019	AY	PS

- NOTES:
- MATERIAL:
LCP BLACK, UL94 V0
 - N = NUMBER OF POSITION PER HOUSING.
 - HOUSING TO BE USED WITH CRIMP CONTACTS
2316113 (AWG 28-24/0.08-0.22 mm2) AND
2316114 (AWG 30-28/0.05-0.08 mm2)
 - PACKAGING : BOX



D



C




CENTERLINE FOR ODD AND EVEN
POSITION HOUSINGS



SINGLE ROW HOUSING,
LATCH VERSION
-5 AS SHOWN

5:1



THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29OCT2017 RAKSHITH R NAYAK	TE Connectivity			
DIMENSIONS: mm		CHK 29OCT2017 RAKSHITH R NAYAK				
		APVD 11DEC2017 PRASHANTH S	NAME AMPMODU 2mm RECEPTACLE, w/B HOUSING, CRIMP, SR, CENTER LATCH			
		PRODUCT SPEC 108-64040-1	-			
MATERIAL SEE NOTE 1		APPLICATION SPEC 114-32173	SIZE A2	CAGE CODE 00779	DRAWING NO C=2316104	RESTRICTED TO -
-		WEIGHT -	CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1
					REV 12	

1-2316104-6	32.1	16
1-2316104-5	30.1	15
1-2316104-4	28.1	14
1-2316104-3	26.1	13
1-2316104-2	24.1	12
1-2316104-1	22.1	11
1-2316104-0	20.1	10
2316104-9	18.1	9
2316104-8	16.1	8
2316104-7	14.1	7
2316104-6	12.1	6
2316104-5	10.1	5
2316104-4	8.1	4
2316104-3	6.1	3
PART NO.	DIM "E"	N

A