




Non-reversing motor starter Size 1 Three phase full voltage Solid-state overload relay OLRelay amp range 3-12A 220-240/440-480VAC 60HZ coil Combination type 30Amp fusible disconnect 30Amp / 250V fuse clip Enclosure NEMA type 1 Indoor general purpose use Standard width enclosure

|                                                                         |                                                     |
|-------------------------------------------------------------------------|-----------------------------------------------------|
| product brand name                                                      | Class 17                                            |
| design of the product                                                   | Non-reversing motor starter with fusible disconnect |
| special product feature                                                 | ESP200 overload relay; Dual voltage coil            |
| <b>General technical data</b>                                           |                                                     |
| weight [lb]                                                             | 34 lb                                               |
| Height x Width x Depth [in]                                             | 24 × 11 × 8 in                                      |
| touch protection against electrical shock                               | NA for enclosed products                            |
| installation altitude [ft] at height above sea level maximum            | 6560 ft                                             |
| ambient temperature [°F]                                                |                                                     |
| • during storage                                                        | -22 ... +149 °F                                     |
| • during operation                                                      | -4 ... +104 °F                                      |
| ambient temperature                                                     |                                                     |
| • during storage                                                        | -30 ... +65 °C                                      |
| • during operation                                                      | -20 ... +40 °C                                      |
| country of origin                                                       | USA                                                 |
| <b>Horsepower ratings</b>                                               |                                                     |
| yielded mechanical performance [hp] for 3-phase AC motor                |                                                     |
| • at 200/208 V rated value                                              | 2 hp                                                |
| • at 220/230 V rated value                                              | 2 hp                                                |
| • at 460/480 V rated value                                              | 0 hp                                                |
| • at 575/600 V rated value                                              | 0 hp                                                |
| <b>Contactor</b>                                                        |                                                     |
| size of contactor                                                       | NEMA controller size 1                              |
| number of NO contacts for main contacts                                 | 3                                                   |
| operating voltage for main current circuit at AC at 60 Hz maximum       | 600 V                                               |
| operational current at AC at 600 V rated value                          | 27 A                                                |
| mechanical service life (operating cycles) of the main contacts typical | 10000000                                            |
| <b>Auxiliary contact</b>                                                |                                                     |
| number of NC contacts at contactor for auxiliary contacts               | 0                                                   |
| number of NO contacts at contactor for auxiliary contacts               | 1                                                   |
| number of total auxiliary contacts maximum                              | 8                                                   |
| contact rating of auxiliary contacts of contactor according to UL       | 10A@600VAC (A600), 5A@600VDC (P600)                 |
| <b>Coil</b>                                                             |                                                     |
| type of voltage of the control supply voltage                           | AC                                                  |
| control supply voltage                                                  |                                                     |
| • at AC at 60 Hz rated value                                            | 220 ... 480 V                                       |
| holding power at AC minimum                                             | 8.6 W                                               |
| apparent pick-up power of magnet coil at AC                             | 218 VA                                              |
| apparent holding power of magnet coil at AC                             | 25 VA                                               |

|                                                                                                                    |                                                     |
|--------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|
| operating range factor control supply voltage rated value of magnet coil                                           | 0.85 ... 1.1                                        |
| percental drop-out voltage of magnet coil related to the input voltage                                             | 50 %                                                |
| ON-delay time                                                                                                      | 19 ... 29 ms                                        |
| OFF-delay time                                                                                                     | 10 ... 24 ms                                        |
| <b>Overload relay</b>                                                                                              |                                                     |
| product function                                                                                                   |                                                     |
| • overload protection                                                                                              | Yes                                                 |
| • phase failure detection                                                                                          | Yes                                                 |
| • asymmetry detection                                                                                              | Yes                                                 |
| • ground fault detection                                                                                           | Yes                                                 |
| • test function                                                                                                    | Yes                                                 |
| • external reset                                                                                                   | Yes                                                 |
| reset function                                                                                                     | Manual, automatic and remote                        |
| trip class                                                                                                         | CLASS 5 / 10 / 20 (factory set) / 30                |
| adjustable current response value current of the current-dependent overload release                                | 3 ... 12 A                                          |
| tripping time at phase-loss maximum                                                                                | 3 s                                                 |
| relative repeat accuracy                                                                                           | 1 %                                                 |
| product feature protective coating on printed-circuit board                                                        | Yes                                                 |
| number of NC contacts of auxiliary contacts of overload relay                                                      | 1                                                   |
| number of NO contacts of auxiliary contacts of overload relay                                                      | 1                                                   |
| operational current of auxiliary contacts of overload relay                                                        |                                                     |
| • at AC at 600 V                                                                                                   | 5 A                                                 |
| • at DC at 250 V                                                                                                   | 1 A                                                 |
| contact rating of auxiliary contacts of overload relay according to UL                                             | 5A@600VAC (B600), 1A@250VDC (R300)                  |
| insulation voltage (Ui)                                                                                            |                                                     |
| • with single-phase operation at AC rated value                                                                    | 600 V                                               |
| • with multi-phase operation at AC rated value                                                                     | 300 V                                               |
| <b>Disconnect Switch</b>                                                                                           |                                                     |
| response value of switch disconnecter                                                                              | 30A / 250V                                          |
| design of fuse holder                                                                                              | Class R fuse clips                                  |
| operating class of the fuse link                                                                                   | Class R                                             |
| <b>Enclosure</b>                                                                                                   |                                                     |
| design of the housing                                                                                              | indoors, usable on a general basis                  |
| <b>Mounting/wiring</b>                                                                                             |                                                     |
| mounting position                                                                                                  | vertical                                            |
| fastening method                                                                                                   | Surface mounting and installation                   |
| type of electrical connection for supply voltage line-side                                                         | Box lug                                             |
| tightening torque [lbf·in] for supply                                                                              | 35 ... 35 lbf·in                                    |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                  | 1x (14 ... 2 AWG)                                   |
| temperature of the conductor for supply maximum permissible                                                        | 75 °C                                               |
| material of the conductor for supply                                                                               | AL or CU                                            |
| type of electrical connection for load-side outgoing feeder                                                        | Screw-type terminals                                |
| tightening torque [lbf·in] for load-side outgoing feeder                                                           | 35 ... 35 lbf·in                                    |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded | 1x (14 ... 2 AWG)                                   |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                     | 75 °C                                               |
| material of the conductor for load-side outgoing feeder                                                            | AL or CU                                            |
| type of electrical connection of magnet coil                                                                       | Screw-type terminals                                |
| tightening torque [lbf·in] at magnet coil                                                                          | 5 ... 12 lbf·in                                     |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                | 2x (16 ... 12 AWG)                                  |
| temperature of the conductor at magnet coil maximum permissible                                                    | 75 °C                                               |
| material of the conductor at magnet coil                                                                           | CU                                                  |
| type of electrical connection for auxiliary contacts                                                               | Screw-type terminals                                |
| tightening torque [lbf·in] at contactor for auxiliary contacts                                                     | 10 ... 15 lbf·in                                    |
| type of connectable conductor cross-sections at contactor for                                                      | 1x (12 AWG), 2x (16 ... 14 AWG), 2x (18 ... 16 AWG) |


|                                                                                                                               |                                                     |
|-------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|
| AWG cables for auxiliary contacts single or multi-stranded                                                                    |                                                     |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible                                          | 75 °C                                               |
| material of the conductor at contactor for auxiliary contacts                                                                 | CU                                                  |
| type of electrical connection at overload relay for auxiliary contacts                                                        | Screw-type terminals                                |
| tightening torque [lbf-in] at overload relay for auxiliary contacts                                                           | 7 ... 10 lbf-in                                     |
| type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded | 2x (20 ... 14 AWG)                                  |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                     | 75 °C                                               |
| material of the conductor at overload relay for auxiliary contacts                                                            | CU                                                  |
| <b>Short-circuit current rating</b>                                                                                           |                                                     |
| design of the fuse link for short-circuit protection of the main circuit required                                             | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| certificate of suitability                                                                                                    | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |
| <b>Further information</b>                                                                                                    |                                                     |

**Industrial Controls - Product Overview (Catalogs, Brochures,...)**  
[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)  
**Industry Mall (Online ordering system)**  
<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17DUC92BC10>  
**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**  
<https://support.industry.siemens.com/cs/US/en/ps/US2:17DUC92BC10>  
**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**  
[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:17DUC92BC10&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17DUC92BC10&lang=en)  
**Certificates/approvals**  
<https://support.industry.siemens.com/cs/US/en/ps/US2:17DUC92BC10/certificate>



CONDUITS TYP. TOP & BOTTOM

| LETTER | CONDUIT SIZE          |
|--------|-----------------------|
| A      | ø12.7 & ø19 CONDUIT   |
| B      | ø25.4 & ø31.8 CONDUIT |



last modified:

1/25/2022