



$$\begin{aligned}\text{Dim } L &= N \times 5.0 \\ \text{Dim } B &= (N-1) \times 5.0\end{aligned}$$

Poles	02	03	04	05	06	07	08	09	10	11	12
Dim L	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00
TOL	±0.10				±0.15				±0.20		

SIGN	DATE	DESCRIPTION	APPROVER
△	02/11/09	The design changed	Jacke
△	02/11/09	The design changed to revoke	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Terminal housing:Thermoplastic (UL94V-0)
- Item b Terminal cover:Thermoplastic (UL94V-0)
- Item c Terminal screw:Steel Zinc plating “-” type
- Item d Clamp:Brass, Ni plated
- Item e Female contact:PhBz , Tin plated

Electrical

- Voltage rating: 300V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 4.5Lb-In
- Screw: M3
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

EO xx 01 x 0 xxxx G

02	2 CONTACTS	0	Black (RAL9005)	0000	Standard @ Logo	RoHS
03	3 CONTACTS	2	Red (RAL3001/D)	000A	Standard ANY Logo	Pb<40,000ppm
...	...	3	Orange(RAL2011/P)			
12	12 CONTACTS	4	Yellow(RAL1018/A)		Any special item by	
		5	Green(RAL6018/T)		customer request,	
		6	Blue (RAL5015/A)		please contact sales	
		8	Grey(RAL7035/D)		department.	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EO 5.0 series (A type Ø1.90mm)					
PART NO.		EOxx01x0xxxxG		DWG NO.		8EO0001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2009.02.23	Jacke 2009.02.23			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: D	X.XX ±0.10
							X° ±1°