

BCH65S04D3

Silicon Carbide Schottky Diode

650V, 4A



Description

BCH65S04D3 utilizes Bestirpower's advanced silicon carbide diode technology. This technology combines the benefits of excellent low forward voltage and robustness. Consequently, the family is suitable for application requiring high power efficiency .



Features

| V_{RRM} | I_F | T_C | Q_C |
|-----------|-------|--------|--------|
| 650 V | 4 A | 154 °C | 9.5 nC |

- High-speed switching
- Low heat dissipation requirements
- Reduce size and cost of the system
- Reduced EMI
- Higher system reliability due to lower operating temperaturest

Applications

- Switch mode power supply
- Solar inverter
- Data Center
- Uninterruptible power supply



Absolute Maximum Ratings ($T_C = 25^{\circ}\text{C}$ unless otherwise noted)

| Symbol | Parameter | | Value | Unit |
|----------------|--|---|-------------|------------------|
| V_{RRM} | Repetitive Peak Reverse Voltage | | 650 | V |
| I_F | Forward Current | $T_C = 25^{\circ}\text{C}$ | 13 | A |
| | | $T_C = 135^{\circ}\text{C}$ | 6 | A |
| | | $T_C = 154^{\circ}\text{C}$ | 4 | A |
| $I_{F,SM}$ | Non-Repetitive Forward Surge Current | $T_C = 25^{\circ}\text{C}, t_p = 10\text{ ms}$ | 39 | A |
| | | $T_C = 110^{\circ}\text{C}, t_p = 10\text{ ms}$ | 32 | A |
| $I_{F,RM}$ | Repetitive Peak Forward Surge Current | $T_C = 25^{\circ}\text{C}, t_p = 10\text{ ms}$ | 34 | A |
| I^2dt value | $\int I^2 dt$ | $T_C = 25^{\circ}\text{C}, t_p = 10\text{ ms}$ | 7 | A ² s |
| | | $T_C = 110^{\circ}\text{C}, t_p = 10\text{ ms}$ | 5 | A ² s |
| P_{tot} | Power Dissipation | $T_C = 25^{\circ}\text{C}$ | 61 | W |
| | | $T_C = 110^{\circ}\text{C}$ | 27 | W |
| | | $T_C = 150^{\circ}\text{C}$ | 10 | W |
| T_J, T_{STG} | Operating Junction and Storage Temperature | | -55 to +175 | °C |

Thermal Characteristics

| Symbol | Parameter | Value | Unit |
|-----------------|--|-------|------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case, Typ. | 2.44 | °C/W |

Electrical Characteristics (T_C = 25°C unless otherwise noted)

| Symbol | Parameter | Test Conditions | Min | Typ | Max | Unit |
|-----------------|---------------------------|--|-----|------|-----|------|
| V _{DC} | DC blocking voltage | | 650 | | | V |
| V _F | Forward Voltage | I _F =4A, T _J =25°C | - | 1.35 | 1.7 | V |
| | | I _F =4A, T _J =175°C | - | 1.7 | 1.9 | |
| I _R | Reverse Current | V _R = 650 V, T _J = 25°C | - | 1 | 20 | µA |
| | | V _R = 650 V, T _J = 175°C | - | 12 | 100 | |
| Q _C | Total Capacitive Charge | V _R = 400 V, T _J = 25°C | - | 9.5 | - | nC |
| C | Total Capacitance | V _R = 0 V, f = 1MHz | - | 185 | - | pF |
| | | V _R = 200 V, f = 1MHz | - | 19 | - | |
| | | V _R = 400 V, f = 1MHz | - | 16.7 | - | |
| E _C | Capacitance Stored Energy | V _R = 400 V, T _C = 25°C | - | 2.4 | - | µJ |

Package Marking and Ordering Information

| Part Number | Top Marking | Package | Packing Method | Quantity |
|-------------|-------------|---------|----------------|----------|
| BCH65S04D3 | BCH65S04D3 | TO220-2 | Tube | 50 units |

Typical Performance Characteristics

Figure 1. Forward Characteristics




Figure 2. Reverse Characteristics




Figure 3. Peak Forward Current Derating




Figure 4. Power Dissipation




Figure 5. Capacitance vs. Reverse Voltage






Figure 6. Capacitance Charge vs. Reverse Voltage





Typical Performance Characteristics

Figure 7. Transient Thermal Impedance



Package Outlines
TO220-2



Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2024 bestirpower – All rights reserved