

SSR 10-32VDC/0-35VDC 5A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Individual relays for TERMSERIES

- Solid-state relays
- Different output versions

General ordering data

Version	TERMSERIES, Solid-state relay, Rated control voltage: 10...32 V DC , Rated switching voltage: 0...35 V DC, Continuous current: 5 A, Plug-in connection
Order No.	1421450000
Type	SSR 10-32VDC/0-35VDC 5A
GTIN (EAN)	4050118235302
Qty.	20 pc(s).

Creation date September 16, 2022 5:13:13 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

SSR 10-32VDC/0-35VDC 5A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	15.7 mm	Depth (inches)	0.618 inch
Height	29 mm	Height (inches)	1.142 inch
Width	12.7 mm	Width (inches)	0.5 inch
Net weight	9.87 g		

Temperatures

Storage temperature	-40 °C...100 °C	Operating temperature	-20 °C...80 °C
---------------------	-----------------	-----------------------	----------------

Probability of failure

MTTF	1,099 Years
------	-------------

Control side

Rated control voltage	10...32 V DC	Nominal control current	3...13 mA
Pull-in/drop-out voltage, typ.	10 V / 8.5 V DC	Status indicator	No

Load side

Rated switching voltage	0...35 V DC	Continuous current	5 A
Rated switching current	5 A	Switch-on delay	< 55 µs
Switch-off delay	< 310 µs	Voltage drop at max. load	≤ 0.3 V
Leakage current	< 20 µA	Min. switching current	1 mA
Protective circuit, load side	Free-wheeling diode	Contact type	1 NO contact (MOS-FET)

General data

Colour	black
--------	-------

Insulation coordination

Dielectric strength for control side - load side	2.5 kV _{eff}	Impulse withstand voltage	2.5 kV
--	-----------------------	---------------------------	--------

Connection data

Wire connection method	Plug-in connection	Pitch in mm (P)	5 mm
------------------------	--------------------	-----------------	------

Classifications

ETIM 6.0	EC001504	ETIM 7.0	EC001504
ETIM 8.0	EC001504	ECLASS 9.0	27-37-16-04
ECLASS 9.1	27-37-16-04	ECLASS 10.0	27-37-16-04
ECLASS 11.0	27-37-16-04	ECLASS 12.0	27-37-16-04

Approvals

Approvals



ROHS

Conform

SSR 10-32VDC/0-35VDC 5A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format


SSR 10-32VDC/0-35VDC 5A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram



View of pins from below

Dimensional drawing

