

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

CM

00

REVISED PER ECO-12-007807

06AUG12

KH

SM

1

UNIT ACCEPTS 1.14 [.045] SQUARE OR ROUND POST.

2

UNIT ACCEPTS STANDARD SL-156 CONTACTS.

3

UNIT ACCEPTS KEYING PLUG 640254-1 AND KEYING PIN 640255-1.

4

CIRCUIT I.D. NUMBER(S),TO BE LOCATED SEQUENTIALLY AS SHOWN.

5

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

OPTIONAL CONSTRUCTION (BOTH CORNERS) UP TO 0.38[.015].

7

ACCEPTS UP TO .110 INCH INSULATION WIRE.

AMP

1

SCALE 10:1

6

2.41
[.095]

TYP

1.37
[.054]

7.93
[.312]

1.37
[.054]

TYP

1

2

3

4

5

6

7

8

9

36.52±0.25
[1.438±.010]

16.76
[.660]

2.54
[.100]

0.927
[.0365]

REF

6.35
[.250]

0.13/25.40
[.005/1.000]

3-DIMENSIONAL MODEL
NTS

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
K. WHITAKER
CHK
D. BOSSI
APVD
D. BOSSI

16NOV2005

16NOV2005

16NOV2005

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0. PLC ± -

1. PLC ± -

2. PLC ± -

3. PLC ± 0.13 [.005]

4. PLC ± -

ANGLES ± 0°30'

FINISH -

TE Connectivity

HOUSING WITH LOCKING RAMP,
SL-156, FOR LARGE WIRE
INSULATION

SIZE
A1

CAGE CODE
00779

DRAWING NO
1744138

RESTRICTED TO
—

SCALE
4:1

SHEET
1

OF
1

REV
B