


做首件确认证线尺寸

REVISION	DESCRIPTION	DATE	DRAFTER
A0	首次发行	22.01.11	Xiu He
A1	线长230改为250	22.02.25	S. He
A2	2.5热缩管改为3.0	22.04.27	S. He
A3	增加铆压高度标准	22.05.23	S. He



- 技术要求:
- 装配要求: TNC尾管与同轴电缆编织间采用铆压(**尾管铆压六角高度3.00-3.15**重点管控), 保持力大于3.5kgf.
 - 方向要求: 无。
 - 电气特性: 特性阻抗:50Ω; 适用频率范围:DC-6GHz;
 - 断短路与高压测试: 100%使用线材综合测试仪测试。
测试条件: 断短路判定值:2kΩ;直流导通电阻:最大2.00Ω;绝缘电阻:DC 300V, 0.05秒, 50MΩ。
 - 拔出力测试: 最小1.30kgf。
测试方法: 沿电缆中心轴, 以约25±3毫米/分钟的速度, 垂直将1.30kg砝码提离桌面即为合格。
 - 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
 - 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
 - 包装规范: 10PCS/扎
 - 环保要求: 产品及其使用之物料皆需要符合RoHS要求。



7	2TA030BK1-015	Ø3.0*L15.0mm, 无卤阻燃, 125H2普通型, 黑色	1	---
6	2LC17S-101	弹垫 T=1.2 镀镍	1	---
5	2LC17S-301	螺母 T=6.0 镀镍	1	---
4	2LC17SM801-7	后塞, 镀镍	1	---
3	2LC17SM801-1	TNC母头公针, 主体+绝缘+针	1	---
2	2LM10P180111	MHF I PLUG FOR OD1.80 CABLE	1	---
1	2C5R17813BN1	RG178透明棕双银线-50 OHM	1	依裁线图裁线
NO	PART NUMBER	PART NAME & DESCRIPTION	Q'TY	REMARKS

GENERAL TOLERANCE:	
LINEAR:	
X	±2.00
X.X	±1.00
X.XX	±0.20
X.XXX	±0.01
ANGLE:	
X°	±4.00°
X.X°	±3.00°
X.XX°	±2.00°
X.XXX°	±1.00°

HJ-Tech 东莞市皇捷通讯科技有限公司	
FILE NAME: 产品图	TITLE: 射频电缆组件
ENG/DATE: Xiu He/22.01.11	RG178透明棕双银线, P1端TNC母头公针, P2端MHF I PLUG, 外露线长250mm
CHE/DATE:	P/N: 3C0619T05-002
APP/DATE:	UNIT: mm
SCALE: 1:1	REVISION: A0
SHEET: 1/1	

COMPLIANCE WITH THE REQUIREMENT: ☒RoHS; ☐HF; ☐SONY SS-00259; ☐OTHERS
*NO USING ESTRICTED AND BANNED SUBSTANCE

H431