




VIEW G-G

NOTES:

1. TERMINAL MATERIAL:
3/4 HARD PHOS BRONZE ALLOY UNS-C51000
2. TERMINAL PLATING:
(1) 30μ"/0.76μ AU OR GXT over 50μ"/1.27μ NICKEL
ON SWAGED TIPS AT MFG. OPTION
(2) 30μ"/0.76μ AU over 50μ"/1.27μ NICKEL
ON SWAGED TIPS AT MFG. OPTION
3. MOLDING MAT'L:
GLASS-FILLED POLYESTER, FLAME RETARDANT
PER UL94V-0, COLOR: BLACK
4. .020/0.51 MAX FLASH PERMISSIBLE AROUND
ALL WINDOWS
5. COMPANY LOGO TO BE MOLDED IN ON DATUM SURFACE
[Z] APPROXIMATELY AS SHOWN
6. .030/0.76 MAX FLASH PERMISSIBLE ON PINS
(BOTH SIDES)
7. OTHER PLATINGS ARE AVAILABLE ON 68419 &
68649. END OF PINS
8. .015/0.38 MAX FLASH PERMISSIBLE ON THIS
END OF PINS.
9. ADD "LF" SUFFIX AT THE END OF PART NUMBER
FOR LEAD FREE OPTION
10. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
11. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.

mat'l. code NOTES 2 & 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM scale 1:1	product family HEADER			
ltr	ecr no	dr	date	tolerances unless otherwise specified		Amphenol FCI	title STRAIGHT HEADER FOR FLAT CABLE RECEIPT			
H				angles	linear					
				0°±2'	.XX±0.01/.X±.3 .XXX±0.005/.XX±.13 .XXXX±0.0020/.XXX±.051					
				dr	COPENHAVER	7/10/84	dwg no			
				enr	P.SMITH	4/10/85	sheet 2 of 4			
				chr	P.SMITH	4/10/85	68648			
				appd	P.SMITH	4/10/85	A3			
sheet index		revision sheet						type Product Customer Drawing		

