




SIGN	DATE	DESCRIPTION	APPROVER
△	2009.03.31	Add the inspection dimension	Jacke
△	2010.05.30	Add cULus standard	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material

- Item ④ Clamp: Brass(CuZn) Ni plated
- Item ⑤ Terminal screw: Steel Zinc plating "-" slot type
- Item ⑥ Female contact: PhBz (CuSn) Tin plated
- Item ⑦ Terminal (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 14-26
- Stranded wire(AWG): 14-26
- Torque: 3.5Lb-In
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: 

KR xx 01 x 0 xxxx G

Pb<40,000ppm

Poles	0	Black (RAL9005)	0000 Standard @ Logo
02 2Contacts	2	Red (RAL3001/D)	000A Standard ANY Logo
02 3Contacts	3	Orange(RAL2011/P)	Any special item by
— ————	4	Yellow(RAL1018/A)	customer request,
24 24Contacts	5	Green(RAL6018/T)	please contact sales
	6	Blue (RAL5015/A)	department.
	8	Grey(RAL7035/D)	

					Δ
	Dim A	Dim B	Dim C	Dim D	
2P	± 0.05	± 0.05	≤ 0.05	≤ 0.05	
3-6p	± 0.15	± 0.15	≤ 0.10	≤ 0.10	
7-12p	± 0.20	± 0.20	≤ 0.20	≤ 0.20	
13-18p	± 0.30	± 0.30			
19-24p	± 0.40	± 0.40			

N = Number of poles
Dim A=Nx5.0
Dim B=(N-1)x5.0

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		KR 5.0mm Series "- " (Without hook)					
PART NO.		KRxx01x0xxxG		DWG NO.		8KR0001	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Jacke 2010.05.30	Jacke 2009.03.31			X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
					UNIT: mm SCALE: NONE SHEET: 01/01 REV.: D		