

PHE841

- EMI suppressor, class X1, metallized polypropylene
- 0.01 – 2.2 μF , 330 VAC, +100°C

RoHS
Compliant

TYPICAL APPLICATIONS

For worldwide use as electromagnetic interference suppressor in all X1 and across-the-line applications.
Not for use in series with the mains.
See www.kemet.com for more information.

CONSTRUCTION

Metallized polypropylene winding, encapsulated in self-extinguishing material meeting the requirements of UL 94 V-0.

TECHNICAL DATA

Rated voltage	330 VAC 50/60 Hz
Capacitance range	0.01 – 2.2 μF
Capacitance tolerance	$\pm 20\%$ standard, $\pm 10\%$ option
Temperature range	-40 to +100°C
Climatic category	40/100/56/B
Approvals	ENEC, UL, cUL


Dissipation factor $\tan\delta$	Maximum values at +23°C			
		$C \leq 0.1 \mu\text{F}$	$0.1 \mu\text{F} < C \leq 1 \mu\text{F}$	$C > 1 \mu\text{F}$
	1 kHz	0.1%	0.1%	0.1%
	10 kHz	0.2%	0.4%	0.8%
	100 kHz	0.6%	—	—

Test voltage between terminals	The 100% screening factory test is carried out at 3000 VDC. The voltage level is selected to meet the requirements in applicable equipment standards. All electrical characteristics are checked after the test.
---------------------------------------	--

Resonance frequency	Tabulated self-resonance frequencies f_0 refer to 5 mm lead length.
----------------------------	---

Insulation resistance	$C \leq 0.33 \mu\text{F}$: $\geq 30\,000 \text{ M}\Omega$ $C > 0.33 \mu\text{F}$: $\geq 10\,000 \text{ s}$
------------------------------	---

In DC applications	Recommended voltage: $\leq 1000 \text{ VDC}$
---------------------------	--



p	d	std l	max l	b
10.0 $\pm$ 0.4	0.6	17	30	± 0.4
15.0 $\pm$ 0.4	0.8	17	30	± 0.4
22.5 $\pm$ 0.4	0.8	6	30	± 0.4
27.5 $\pm$ 0.4	0.8	6	30	± 0.4
37.5 $\pm$ 0.5	1.0	6	30	± 0.7

Tolerance in lead length
 $< 30 \text{ mm}$ $^{+0}_{-1} \text{ mm}$
 30 mm $^{+5}_{-0} \text{ mm}$

ENVIRONMENTAL TEST DATA

Endurance	EN/IEC 60384-14:2005	1.25 x U_R VAC 50 Hz, once every hour increased to 1000 VAC for 0.1 s, 1000 h at upper rated temperature	
Vibration	IEC 60068-2-6 Test Fc	3 directions at 2 hours each, 10–55 Hz at 0.75 mm or 98 m/s ²	No visible damage No open or short circuit
Bump	IEC 60068-2-29 Test Eb	1000 bumps at 390 m/s ²	No visible damage No open or short circuit
Change of temperature	IEC 60068-2-14 Test Na	Upper and lower rated temperature 5 cycles	No visible damage
Active flammability	EN/IEC 60384-14:2005		
Passive flammability	EN/IEC 60384-14:2005	Enclosure material of UL94V-0 flammability class	
Humidity	IEC 60068-2-3 Test Ca	+40°C and 90 – 95% R.H.	56 days

ARTICLE TABLE

Capaci- Box Max dimensions
tance code in mm
 μF B H L f_o Max
MHz dU/dt Article code
V/ μs

LEAD SPACING 10 MM

0.010	A02	4.5	10.5	13.0	11	100	PHE841EA5100MR17
0.012	A03	5.0	11.0	13.0	10	100	PHE841EA5120MR17
0.015	A03	5.0	11.0	13.0	9.4	100	PHE841EA5150MR17
0.018	A04	6.0	12.0	13.0	8.7	100	PHE841EA5180MR17
0.022	A04	6.0	12.0	13.0	8.1	100	PHE841EA5220MR17

LEAD SPACING 15 MM

0.010	B04	5.5	10.5	18.0	10	100	PHE841EB5100MR17
0.012	B04	5.5	10.5	18.0	9.4	100	PHE841EB5120MR17
0.015	B04	5.5	10.5	18.0	8.7	100	PHE841EB5150MR17
0.018	B04	5.5	10.5	18.0	7.9	100	PHE841EB5180MR17
0.022	B05	5.5	12.5	18.0	7.2	100	PHE841EB5220MR17
0.027	B15	6.0	12.0	18.0	6.5	100	PHE841EB5270MR17
0.033	B10	6.5	12.5	18.0	5.9	100	PHE841EB5330MR17
0.039	B06	7.5	14.5	18.0	5.4	100	PHE841EB5390MR17
0.047	B06	7.5	14.5	18.0	5.0	100	PHE841EB5470MR17
0.056	B12	8.0	15.0	18.0	4.6	100	PHE841EB5560MR17
0.068	B11	8.5	16.0	18.0	4.2	100	PHE841EB5680MR17
0.082	B14	9.5	17.5	18.0	3.8	100	PHE841EB5820MR17
0.10	B14	9.5	17.5	18.0	3.7	100	PHE841EB6100MR17

LEAD SPACING 22.5 MM

0.068	D13	6.5	14.5	26.0	2.9	100	PHE841ED5680MR06L2
0.082	D17	7.0	16.5	26.0	2.8	100	PHE841ED5820MR06L2
0.10	D17	7.0	16.5	26.0	2.7	100	PHE841ED6100MR06L2
0.12	D14	8.0	16.0	26.0	2.6	100	PHE841ED6120MR06L2
0.15	D15	9.0	18.5	26.0	2.5	100	PHE841ED6150MR06L2
0.18	D18	10.5	19.0	26.0	2.3	100	PHE841ED6180MR06L2
0.22	D18	10.5	19.0	26.0	2.2	100	PHE841ED6220MR06L2
0.27	D16	11.0	21.5	26.0	2.0	100	PHE841ED6270MR06L2
0.33	D16	11.0	21.5	26.0	1.9	100	PHE841EY6330MR06L2 *
0.39	D19	15.5	24.5	26.0	1.6	100	PHE841ED6390MR06L2
0.47	D19	15.5	24.5	26.0	1.5	100	PHE841ED6470MR06L2

Capaci- Box Max dimensions
tance code in mm
 μF B H L f_o Max
MHz dU/dt Article code
V/ μs

LEAD SPACING 27.5 MM

0.22	F11	10.5	20.5	31.5	2.0	100	PHE841EF6220MR06L2
0.27	F11	10.5	20.5	31.5	1.8	100	PHE841EF6270MR06L2
0.33	F12	11.5	22.5	31.5	1.6	100	PHE841EF6330MR06L2
0.39	F03	13.5	23.0	31.5	1.4	100	PHE841EF6390MR06L2
0.47	F03	13.5	23.0	31.5	1.3	100	PHE841EF6470MR06L2
0.56	F13	14.5	24.5	31.5	1.2	100	PHE841EF6560MR06L2
0.68	F14	17.5	28.0	31.5	1.1	100	PHE841EF6680MR06L2
0.82	F15	19.0	29.0	31.5	1.0	100	PHE841EF6820MR06L2
1.0	F16	21.0	30.0	31.5	1.0	100	PHE841EF7100MR06L2

LEAD SPACING 37.5 MM

0.68	R05	13.0	24.0	41.0	1.1	100	PHE841ER6680MR06L2
0.82	R04	15.0	26.0	41.0	1.0	100	PHE841ER6720MR06L2
1.0	R04	15.0	26.0	41.0	0.92	100	PHE841ER7100MR06L2
1.2	R02	16.5	32.0	41.0	0.84	100	PHE841ER7120MR06L2
1.5	R03	19.0	36.0	41.0	0.74	100	PHE841ER7150MR06L2
1.8	R06	21.0	38.0	41.0	0.67	100	PHE841ER7180MR06L2
2.2	R06	21.0	38.0	41.0	0.60	100	PHE841ER7220MR06L2

* Only $\pm 20\%$

APPROVALS

Certification Body	Specification
ENEC	EN/IEC 60384-14:2005
UL	UL 60384-14
	CAN/CSA-E60384-14:09

MARKING

- RIFA
- RIFA article code
- Rated capacitance
- Capacitance tolerance code
- Rated voltage
- X1
- Approval marks
- Manufacturing date code
- IEC climatic category
- Passive flammability class

ORDERING INFORMATION

The article code for the standard part is given in the article table.

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.