


1. 产品尺寸图Product Dimension Drawing



2. 产品电器参数Product electrical parameters

防护等级 (Ingress protection)	IP50	
插拔测试 (Plugging and unplugging test)	<500次	
产品耐温 (The product is temperature resistant)	-20° C / +85° C	
盐雾腐蚀 (Salt Spray Corrosion)	>48 hr	
额定电流Current rating	5A	
额定电压 (Rated voltage)	150V	
工作电压 (AC.V)	400	
Operating voltage (AC.V)	1500	
耐电压 (AC.V)	2000	
Withstand voltage (AC.V)	10	
绝缘阻抗 (mΩ) DC500V		
Insulation Resistance (mΩ)DC500V		
绝缘电阻 (mΩ) DC1A		
Insulation Resistance (mΩ)DC1A		

3. 环境及表面处理产品特性Environmental and surface treatment product characteristics

外壳材料 Housing material	锌合金镀镍Zinc alloy nickel plating
绝缘体材料 Insulator material	橡胶黑木Rubber black wood
触体材料 Contact material	黄铜镀银Brass silver-plated

1: 连接器组装生产所有公差通常为0.1mm,2: 插座直接拧入螺纹孔中, 螺纹 +0.05mm
1: All tolerances are usually 0.1mm for connector assembly production, 2: The socket is screwed directly into the threaded hole, the thread is +0.05mm