


1	2	3	4	5	6	7	8
A					REVISION	DESCRIPTION	DATE
					A1	“单壁热塑套管”变更为“双壁含胶性”	18.05.25
B					A2	“印字LOGO”变更为“丝印LOGO”	18.08.01
C					A3	变更剥线尺寸和焊接工艺	21.07.07
D					A4	变更接头、测试标准VSMR小于2.0、加EVA	21.09.26
E					A5	环焊后塞改为铆压后塞	S. He
F							



No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS
GENERAL TOLERANCE: LINEAR: X ± 0.20 X. X ± 0.15 X. XX ± 0.05 X. XXX ± 0.01				
9	2MH106	EVA 黑色 L45.0*W10.0*T1.0mm, EVA+单面3M 9448A 背胶	1	---
8	2YC006	铜片, L8.20*W4.00*H4.20*T0.5 磷铜	1	---
7	2TC064BK0-025	热缩管, 双壁含胶型, 6.40*L25.0, 黑色	1	---
6	2YP013	L95.00*W13.50, 铜箔喷绿油, 焊锡点区域镀锡	1	---
5	2SBKG2022	L112.00*W18.00, ABS黑色丝印“大象”	1	---
4	2SBKG2012	L112.00*W18.00mm, ABS黑色丝印“MOMA”	1	---
3	2LC15PS022-8	主体+胶芯+后塞	1	---
2	2LC15PS022-5	SMA 母针OD1.8*L7.8mm, 镀金3u''	1	---
1	2C5A14111BK1	微细同轴电缆SFX-141	1	---

GENERAL TOLERANCE: LINEAR: X ± 0.20 X. X ± 0.15 X. XX ± 0.05 X. XXX ± 0.01	HJ-Tech	东莞市皇捷通讯科技有限公司
FILE NAME:	产品图	TITLE: 射频天线组件
ENG/DATE:	DENG JUN. TAN/18.04.17	外置直连式; G20黑色, PCB结构, 141黑色+SMA公头母针, 外露长度47mm, 丝印“大象图标”“MOMA”
CHE/DATE:		P/N: 3D2001BK00-003
APP/DATE:		UNIT: mm
		SCALE: 1:1
		REVISION: A0
		SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: RoHS; HF; SONY SS-00259; OTHERS
*NO USING RESTRICTED AND BANNED SUBSTANCE

H431