







LOC		DIST		REVISIONS						
CM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD	
			A	REVISED PER ECR-12-005286			22MAR2012	KH	TM	

1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.

△ CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [.062] THICK P.C. BOARD

PHOSPOR BRONZE, PRE-TIN		NYLON, UL94V-2, NATURAL		2029402-1	
SOCKET CONTACT MATERIAL AND FINISH		HOUSING MATERIAL AND COLOR		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH CHK TOM MICHELUTTI APVD TOM MICHELUTTI		TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.13 (.005) 3 PLC ± 4 PLC ± ANGLES ±0° 30'		NAME SOCKET HEADER ASSEMBLY, 3 CIRCUIT, UNIVERSAL MATE-N-LOK™	
		APPLICATION SPEC		SIZE A100779	
MATERIAL SEE TABLE		FINISH SEE TABLE		CAGE CODE C=2029402	
		WEIGHT -		DRAWING NO A100779	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 8:1	
				SHEET 1 OF 1	
				REV A	