


DUAL OPERATIONAL AMPLIFIER

DESCRIPTION

JRC4580 is the dual operational amplifier, specially designed for improving the tone control, which is most suitable for the audio application. Featuring noiseless, higher gain bandwidth, high output current and low distortion ratio, and it is most suitable not only for acoustic electronic part of audio pre-amp and active filter, but also for the industrial measurement tools. It is also suitable for the head phone amp at higher output current. And further more, it can be applied for the handy type set operational amplifier of general purpose in application of low voltage single supply type which is properly biased of the input low voltage source.

FEATURE


- Operating Voltage: $\pm 2V \sim \pm 16V$.
- Low Input Noise Voltage: $0.8\mu V_{rms}$ Typ.
- Wide Gain Bandwidth Product: 15mhz Typ.
- Low Distortion: 0.0005% Typ.
- Slew Rate: $5V/\mu A$ Typ.
- Package Outline DIP-8、SOP-8、DFN-8 and MSOP-8 .
- Bipolar Technology.




Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
JRC4580PG	DIP-8	4580	TUBE	2000pcs/box
JRC4580DRG	SOP-8	4580	REEL	2500pcs/reel
JRC4580DRG4	SOP-8	4580	REEL	4000pcs/reel
JRC4580DGKRG	MSOP-8	4580	REEL	3000pcs/reel
JRC4580DQRG	DFN-8 3*3	4580	REEL	5000pcs/reel

PIN CONFIGURATION



EQUIVALENT CIRCUIT



ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

Characteristic		Symbol	Value	Unit
Supply Voltage		V+/V-	±16	V
Input Voltage		V _{IC}	±15	V
Differential Input Voltage		V _{ID}	±30	V
Output Current		I _O	±50	mA
Power Dissipation	DIP-8	P _D	800	mW
	SOP-8		300	
	MSOP-8		250	
Operating Temperature Range		T _{OPR}	-40~85	°C
Storage Temperature Range		T _{stg}	-40~125	°C
Lead Temperature (Soldering, 10 seconds)		T _L	245	°C

Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured.


ELECTRICAL CHARACTERISTICS

(Unless otherwise specified: Ta= 25°C, V+/V- =±15V)


Parameter	Symbol	Test condition	Min	Typ	Max	Unit
Input Offset Voltage	V _{IO}	R _s ≤ 10 kΩ		0.5	3	mV
Input Offset Current	I _{IO}			5	200	nA
Input Bias Current	I _B			100	500	nA
Large Signal Voltage Gain	A _v	R _L ≥ 2kΩ, V _O = ±10V	90	110		dB
Output Voltage Swing	V _{OM}	R _L ≥ 2kΩ	±12	±13.5		V
Input Common Mode Voltage Range	V _{ICM}		±12	±13.5		V
Common Mode Rejection Ratio	CMR	R _s ≤ 10 kΩ	80	110		dB
Supply Voltage Rejection Ratio	SVR	R _s ≤ 10 kΩ	80	110		dB
Operating Current	I _{CC}			6	9	mA
Slew Rate	SR	R _L ≥ 2kΩ		5		V/μs
Gain Bandwidth Product	GB	f=10kHz		15		MHz
Total Harmonic Distortion	THD	A _v =20dB, V _O = 5 V, f=1kHz, R _L =2kΩ		0.0005		%
Input Noise Voltage	V _{NI}	RIAA R _s =2.2kΩ, 30kHz LPF		0.8		μVrms

CHARACTERISTICS CURVES


Maximum Output Voltage Swing vs. Load Resistance




Maximum Output Voltage Swing vs. Frequency




Output Voltage Swing vs. Output Current




Equivalent Input Noise Voltage vs. Frequency



Operating Current vs. Temperature




Output Voltage Swing vs. Temperature




TYPICAL CHARACTERISTICS


Input offset Voltage vs. Temperature




Input bias current vs. Temperature




Maximum Output Voltage Swing vs. Operating Voltage




Operating Current vs. Operating Voltage



Total Harmonic Distortion vs. Output Voltage




Voltage Gain Phase vs. Frequency



PHYSICAL DIMENSIONS


DIP-8



Dimensions In Millimeters(DIP-8)

Symbol:	A	B	D	D1	E	L	L1	a	b	c	d
Min:	6.10	9.00	8.10	7.42	3.10	0.50	3.00	1.50	0.85	0.40	2.54 BSC
Max:	6.68	9.50	10.9	7.82	3.55	0.70	3.60	1.55	0.90	0.50	

SOP-8 (150mil)




Dimensions In Millimeters(SOP-8)

Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	1.35	0.05	4.90	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	5.10	6.20	4.00	0.80	8°	0.45	

PHYSICAL DIMENSIONS


MSOP-8



Dimensions In Millimeters(MSOP-8)

Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.80	0.05	2.90	4.75	2.90	0.35	0°	0.25	0.65 BSC
Max:	0.90	0.20	3.10	5.05	3.10	0.75	8°	0.35	

DFN-8 3*3



Dimensions In Millimeters(DFN-8 3*3)

Symbol:	A	A1	B	B1	E	F	a	b
Min:	0.85	0.00	2.90	2.90	0.20	0.30	0.20	0.65 BSC
Max:	0.95	0.05	3.10	3.10	0.25	0.50	0.34	

REVISION HISTORY

REVISION NUMBER	DATE	REVISION	PAGE
V1.0	2014-6	New	1-9
V1.1	2024-8	Document reformatting	1-9

IMPORTANT STATEMENT:

Hanschip Semiconductor reserves the right to change its products and services without notice. Before ordering, the customer shall obtain the latest relevant information and verify whether the information is up to date and complete. Hanschip Semiconductor does not assume any responsibility or obligation for the altered documents.

Customers are responsible for complying with safety standards and taking safety measures when using Hanschip Semiconductor products for system design and machine manufacturing. You will bear all the following responsibilities: select the appropriate Hanschip Semiconductor products for your application; Design, validate and test your application; Ensure that your application meets the appropriate standards and any other safety, security or other requirements. To avoid the occurrence of potential risks that may lead to personal injury or property loss.

Hanschip Semiconductor products have not been approved for applications in life support, military, aerospace and other fields, and Hanschip Semiconductor will not bear the consequences caused by the application of products in these fields. All problems, responsibilities and losses arising from the user's use beyond the applicable area of the product shall be borne by the user and have nothing to do with Hanschip Semiconductor, and the user shall not claim any compensation liability against Hanschip Semiconductor by the terms of this Agreement.

The technical and reliability data (including data sheets), design resources (including reference designs), application or other design suggestions, network tools, safety information and other resources provided for the performance of semiconductor products produced by Hanschip Semiconductor are not guaranteed to be free from defects and no warranty, express or implied, is made. The use of testing and other quality control technologies is limited to the quality assurance scope of Hanschip Semiconductor. Not all parameters of each device need to be tested.

The documentation of Hanschip Semiconductor authorizes you to use these resources only for developing the application of the product described in this document. You have no right to use any other Hanschip Semiconductor intellectual property rights or any third party intellectual property rights. It is strictly forbidden to make other copies or displays of these resources. You should fully compensate Hanschip Semiconductor and its agents for any claims, damages, costs, losses and debts caused by the use of these resources. Hanschip Semiconductor accepts no liability for any loss or damage caused by infringement.