







LOC	DIST	REVISIONS						
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			K	REVISED PER ECO-12-014566	18DEC2012	JY	AC	
			L	UPDATE NICKEL PLATING THICKNESS	20JUN2017	JW	SH	
			M	REVISED PER ECR-19-009785	24JUN2019	IT	SH	
			M1	CHANGE SLOT TO 1.3 MAX	27AUG2019	IT	SH	




- PART COMPATABLE WITH SFP MSA. REFER TO THE SFP MSA FOR DIMENSIONS NOT SHOWN ON THIS PRINT.
- HOUSING: HIGH TEMPERATURE LCP, UL 94V-0 RATED, BLACK. CONTACT: PHOSPHOR BRONZE.
- CONTACTS: 0.00038 MIN GOLD IN CONTACT AREA, 0.00013 MIN GOLD ON SOLDER AREA, OVER 0.00127 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- PACKAGED 480 PIECES PER REEL.
- DATUMS AND BASIC DIMENSIONS TO BE ESTABLISHED BY CUSTOMER, SEE DRAWING 1367034 FOR LAYOUT WHEN USED WITH 1367034-1 BOTTOM CAGE (STANDARD SFP APPLICATION).
- CONTACTS: 0.00076 MIN GOLD IN CONTACT AREA, 0.00013 MIN GOLD ON SOLDER AREA, OVER 0.00127 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.



SCALE 8:1



DETAIL H
SCALE 25:1






SEE PAGE 2		1367073-6
YES		1367073-4
YES		1367073-3
NO		1367073-2
NO		1367073-1
DATE CODE	FINISH	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. KERLIN 01MAR2000	 TE Connectivity	
DIMENSIONS:		CHK E. BRIGHT 01MAR2000		
mm		APVD F. BRIGHT 01MAR2000	NAME	
		PRODUCT SPEC 108-1949	PT CONNECTOR ASSEMBLY, 20 POSITION SFP, RTANG, 0.8MM	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC 114-13017	SIZE	
		WEIGHT -	CAGE CODE DRAWING NO	
MATERIAL	FINISH 	RESTRICTED TO		
		A100779C=1367073		
SEE TABLE		SCALE 12:1 SHEET 1 OF 3 REV M		
		Customer Drawing		

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

1367073-6 AS SHOWN
PRINT PART NUMBER AND DATE CODE ON TOP
ALL OTHERS SAME AS 1367073-1



1367073-1 AS SHOWN
SCALE 11:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. KERLIN	01MAR2000	 TE Connectivity		
		CHK E. BRIGHT	01MAR2000			
DIMENSIONS:		APVD F. BRIGHT	01MAR2000	NAME PT CONNECTOR ASSEMBLY, 20 POSITION SFP, RTANG, 0.8MM	RESTRICTED TO -	
mm		PRODUCT SPEC				
		108-1949				
		APPLICATION SPEC				
		114-13017				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT		A100779C=1367073		
0 PLC ±		-		SCALE 12:1		
1 PLC ±				SHEET 2 OF 3		
2 PLC ±0.10				REV M		
3 PLC ±						
4 PLC ±						
ANGLES ±						
FINISH						
MATERIAL		Customer Drawing				

