




PCB LAYOUT

Poles	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16
Dim A	13.0	20.5	28.0	35.5	43.0	50.5	58.0	65.5	73.0	80.5	88.0	95.5	103.0	110.5	118.0
Dim B	7.5	15.0	22.5	30.0	37.5	45.0	52.5	60.0	67.5	75.0	82.5	90.0	97.5	105.0	112.5
TOL	±0.15				±0.25				±0.35						

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.01.25	Add cULus standard	Jacke
△	2010.01.25	The design is changed	Jacke
△	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

- Item a Terminal body:Thermoplastic (UL94V-0)
- Item b Terminal Cover:Thermoplastic (UL94V-0)
- Item c Female contact:PhBz(CuSn),Tin plated

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 245°C±10°C/5 Sec

△ ● Safety Approval: cULus

V7 xx A 1 x 0 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
16 16 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request. please contact sales department.

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 7.5 Series Vertical (2P~16P)			
PART NO.	V7xxA1x0xxxxG			DWG NO.	8V704.01
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Jacke	Jacke		
		2010.03.31	2010.01.26		
				SHEET: 01/01	REV.: D
				UNIT: mm	X. ±0.5
				SCALE: 1/4	X.X ±0.3
					X.XX ±0.1
					X° ±1°