




THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.


THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
SA25594



SCALE 8:1

- NOTE:
1. MATERIALS: AS NOTED.
 2. PLATING: TIN PLATED.
 3. SURFACE TREATMENT : IRIDITE OVER CADMIUM PLATE.
- * THESE SIZES NOT IRIDITED.




PROPER SELECTION OF HYRINGS:

OUTER FERRULES MAY BE USED IN COMBINATION WITH ANY INNER FERRULES, DEPENDING ON THE SIZE OF THE CONDUCTOR, THE THICKNESS OF THE SHIELD AND THE SIZE OF THE GROUND TAP. HOWEVER, DUE TO VARIATION IN INSULATION DIAMETER AND BRAID CONSTRUCTION, THE RECOMMENDED BASIS FOR SIZE SELECTION FOR SHIELDED CABLE IS A FACTORY-INSTALLED, SAMPLE CONNECTION MADE ON ACTUAL WIRE TO BE USED. IF IT IS NOT CONVENIENT TO FORWARD WIRE SAMPLES, SIZES CAN BE DETERMINED AS FOLLOWS:

DETERMINE O.D. OF INNER INSULATION. SELECT INNER HYRING FROM CHART ABOVE HAVING I.D. A MINIMUM OF .005 GREATER THAN THIS DIAMETER. TO THE O.D. OF THIS FERRULE ADD .025 (FOR SINGLE BRAID) PLUS .040 FOR WIRE TAP (UPTO #18), IF USED, AND SELECT OUTER FERRULE HAVING I.D. ATLEAST EQUAL TO THIS FIGURE. THE PROPER CRIMPING TOOL FOR EACH OUTER HYRING IS LISTED ON TABLE.

OUTER HYRING								
L=.25		DIAMETER (IN INCH.)		INSTALLATION TOOLS				
				RATCHET HYTOOLS		HYTOOLS	HYPRESSES	
CAT. NO.	COLOR	I.D.	O.D.	MR8PV TYPE INCLUDES DIE	M8ND DIE SET NO.	Y10R Y10C-1 DIE SET NO.	Y10NCP DIE SET NO.	Y8ND DIE SET NO.
YOC70	*TIN	.101	.124	MR8PV-14S		R7VST		
YOC80	BLUE	.125	.156	MR8PV-S	N8VST	R8VST		N8VST
YOC90	PURPLE	.149	.179	MR8PV-S, MR8PV-1S	N10VST	R14VST-5		N10VST
YOC100	YELLOW	.156	.196	MR8PV-S, MR8PV-1S	N10VST	R14VST-5		N10VST
YOC110	BLUE	.180	.204	MR8PV-S, MR8PV-1S	N10VST	R14VST-5		N10VST
YOC112	BLUE	.175	.215	MR8PV-S, MR8PV-1S	N12VST	R14VST-5		N12VST
YOC120	ORANGE	.187	.227	MR8PV-S, MR8PV-1S	N12VST	R14VST-5		N12VST
YOC128	*TIN	.199	.235	MR8PV-S, MR8PV-1S	N12VST	R14VST-5		N12VST
YOC130	YELLOW	.207	.243	MR8PV-S, MR8PV-1S MR8PV-10S	N12VST N13VST	R14VST-5 R14VST-3		N12VST N13VST
YOC140	GREEN	.219	.250	MR8PV-1S MR8PV-11S	N14VST	R14VST-5		N14VST
YOC150	ORANGE	.235	.266	MR8PV-2	N16VT	R18VT-3		N16VT
YOC160	YELLOW	.261	.297	MR8PV-2	N16VT	R18VT-3		N16VT
YOC180	PURPLE	.281	.331	MR8PV-2		R18VT-3		
YOC190	GREEN	.300	.335	MR8PV-2		R18VT-3		
YOC200	YELLOW	.312	.362	MR8PV-3		R20VT		
YOC220	ORANGE	.344	.394	MR8PV-4 MR8PV-11S		R22VT		
YOC240	BLUE	.375	.406	MR8PV-7		R24VT		
YOC250	RED	.405	.453	MR8PV-6		R25VT		
YOC320G1	PURPLE	.500	.550			R29VT		
YOC371G1	*TIN	.580	.620			R32VT		
YOC370	*TIN	.705	.755	MD5-36				

INNER HYRING			
L=.31		DIAMETER (IN INCH.)	
		I.D.	O.D.
YIC046	*TIN	.046	.070
YIC058	YELLOW	.058	.083
YIC063	RED	.063	.088
YIC071	GREEN	.071	.096
YIC080	BLUE	.080	.104
YIC090	ORANGE	.090	.114
YIC101	YELLOW	.101	.124
YIC109	RED	.109	.131
YIC115	*TIN	.115	.146
YIC124	GREEN	.124	.145
YIC125	YELLOW	.125	.156
YIC134	ORANGE	.134	.156
YIC150	BLUE	.150	.181
YIC156	RED	.166	.191
YIC180	GREEN	.180	.204
YIC194	BLUE	.194	.255
YIC219	*TIN	.219	.243
YIC261	BLUE	.261	.297
YIC297	RED	.297	.337
YIC375G1	*TIN	.375	.423
YIC472G1	*TIN	.472	.516
YIC495G1	*TIN	.495	.535
YIC340	*TIN	.340	.390

LINEAR MEASURE:			INCH [mm]
THIRD ANGLE PROJECTION			
			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	INCH [mm]		
ONE PLACE	±.1 [±3]		
TWO PLACES	±0.02 [±.5]		
THREE PLACES	±0.005		
ANGLES ±1°			

SUPERSEDES: SA-25594-16

DRAWING TITLE				
COLORED FERRULES				
CAT NO. YIC & YOC _ _ _ _ (SEE TABLE)				
CAGE NO: 09922		SIZE: B		
CUSTOMER		 www.souriau.com	APPROVAL	
			DRAWN: NVM 11-14 -11	
			CHKD : SDH 11-14 -11	
			DSGN : XXX mm-dd-yy	
			MFG : DH 11-14 -11	
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M-1994.			QC : BB 11-14 -11	
			DRAWING SCALE: 8:1	
			DRAWING NO. REV	
			SA25594 W	
			1 OF 1	

B

A