





DIMENSION

Dim A	Nx5.08+1.52
Dim B	(N-1)x5.08
Dim C	(N-1)x5.08+10.16
Dim D	Nx5.08+11.32
Dim E	(N-1)x5.08

N= NUMBER OF CONCATS

Poles	Tolerance
2P-6P	±0.20
7P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40





SECTION: L-L

V5 xx 51 x 5 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
... ..
24 24 CONTACTS

Color
0 Black (RAL9005)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
C Green(RAL6018/U)

G RoHS compliant (lead<4%)
In copper Alloy
0000: "®" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request.
please contact sales



SECTION P-P

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.12.29	The design is changed from the round hole to hexagonal hole	Jacke
△	2009.12.29	The current rating and torque(Lb-In) is changed	Jacke
△	2010.10.11	The design is changed	Jacke
△	2011.08.17	Torque(Lb-In) is changed from 5.2(Lb-In) to 4.4(Lb-In)	Aaron
△	2011.08.17	Add is cULus	Aaron
△	2011.08.18	The dimension are added	Aaron
△	2012.02.07	Add the positioning rib on rail slot base to prevent install wrongly.	Aaron
△	2012.04.09	Change the structure of nut and add the glue process	Venter

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- Material:
- Item ① Clamp: Brass, Ni plated
 - Item ② Terminal(housing): Thermoplastic (UL94V-0)
 - Item ③ Terminal(cover): Thermoplastic (UL94V-0)
 - Item ④ Contact pin : Brass,Tin plated.
 - Item ⑤ Terminal screw: Steel, Zinc plating solt "--"type M3
 - Item ⑥ Terminal(track): Thermoplastic (UL94V-0)
 - Item ⑦ With flange nut: Brass M2.5

Electrical: cULus

- Voltage rating:300V
- Current rating: 12A
- Wire range:
 - Solid wire(AWG):12-30
 - Stranded wire(AWG):12-30
- △ ● Torque(Lb-In): 4.4
- Screw:M3
- Wire strip length: 6-7 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Safety Approval: cULus
- Critical dimension: △

ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

CUSTOMER COPY

TITLE		V5 - 5.08 Series 2P-24P (With Flange) Dinrail holder B type			
PART NO.		V5xx51x5xxxxG		DWG NO.	8V50001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Venter 2012.04.09	Venter 2012.04.09		
					Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
				UNIT: mm SCALE: NONE SHEET: 01/01 REV.: G	