







P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	24OCT2021	A.Z	E.J



2363012-1 AS SHOWN




SCALE 1:1

- 1 THE SEALING SHOULD BE FULLY INSERTED AND ALL RIBS OF THE SOCKET HOUSING SHOULD BE INSIDE OF THE CORRESPONDING POCKETS OF THE PERIPHERAL SEAL
- 2 ASSY DELIVERED WITH SECOND LOCK/CPA IN PRE-LOCK POSITION
- 3 APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZES:

7-1452665-1	0.35	Ø1.2~Ø1.4	967067-2	967056-1
7-1452671-1	1.0~1.5	Ø1.90~Ø2.40	2287497-1	967056-1
7-1452668-1	0.5~0.75	Ø1.40~Ø1.90	0-967067-1	967056-1
TERMINAL P/N	WIRE SIZE (mm2)	INSULATION WIRES(mm)	SWS P/N	BLIND PLUG P/N

1	PA46-GF15	GREY	CPA	4
1	SILICON RUBBER	NATURE	SEAL	3
1	PA6 GF18	RED	SECOND LOCK	2
1	PA6 GF15	BLACK	HOUSING	1
2363012-1	MATERIAL	COLOR	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. PENG CHK E. JIANG APVD I. YIN		13DEC2019 13DEC2019 13DEC2019		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 10POS,MCON 1.2,REC HSG ASSY			
		0 PLC ± 1 PLC ±0.8 2 PLC ±0.5 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC -		-	
		FINISH		APPLICATION SPEC 114-32350		SIZE A2	
		MATERIAL - -		WEIGHT -		CAGE CODE 00779	
				CUSTOMER DRAWING		DRAWING NO C-2363012	
						RESTRICTED TO -	
						SCALE 2:1	
						SHEET 1 OF 1	
						REV A	