

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929

ACTUATOR-SWITCH

JS-223

M

**DRAWING
NUMBER**

X

✕

31

3

REPLACES

RELEASE NO. SR-7354

CHECK

REVISIONS

A CO16763

D W V

5 MAR 62

B **CO21422**

W E 8
20 JUNE 66

--	--

CHECK

五

Mac

12

1

312

3	CK
---	----

CHE

1.

Ma

19

7

2

CHFC

1.

1

1

1

1.

.09 WIDE X .031 THICK LEVER.

CORROSION RESISTANT STEEL ACTUATOR AND BRACKET (TYPE 302).

.125 APPROX. PRETRAVEL

.406 APPROX. OPERATING POSITION

.16

.025

1.03 R.

.09

.12

.34

.09

.088

.098^{+0.002}_{-.004}

REF.

.375

.828 REF.

.25

.088 DIA. HOLE

.281

REF.

DOTTED LINES INDICATE BASIC SWITCH IN PLACE.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
WITH ISMI BASIC IN PLACE					
OPERATING FORCE ----- 1 OZ. MAX. RELEASE FORCE ----- 4 GRAMS MIN. DIFFERENTIAL TRAVEL----- .030 MAX. OVERTRAVEL----- .030 MIN.		CONTACT ARRANGEMENT		BREAK DISTANCE	
				DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±	
				WEIGHT	