






Technical specification:

Rated voltage: IEC 61076-2-101	250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +85°C
Mating cycles: IEC 60512-9a	>=100
Wire cross section:	AWG20 / max. 0,5 mm ²


Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PA6, UL 94
Clamp/ screw contact:	Stainless steel / steel nickel plated
Cable seal:	Elastomere
O-Ring:	FPM
Coupling nut:	GD-Zn, nickel plated
Housing:	GD-Zn, nickel plated

Installation specification:

Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 18: 36-000240

Part no:	Description:	Pos:	Cable-Ø:
Clamp connection 43-00073	SAL - 12B - RKC4 - K8	4	6 - 8,5 mm
Screw connection 43-00075	SAL - 12B - RKC4 - S8	4	6 - 8,5 mm

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant	Index: a 07.02.11 dbu Ä3903 Coupling nut modified, spanner flats added, data sheet modified	 dim. in mm	title: Female connector M12x1, field attachable, axial, with clamp/ screw connection, Profibus DP
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		

	date	name
drawn	07.02.08	Franz
appd.	11.02.08	Schmidt

CONEC®

dwg no:	43K1A513
part no:	see table