

SIGN	DATE	DESCRIPTION	APPROVER
△	06/26'06	Voltage rating is changed from 250V to 300V	Marvin
△	06/26'06	Current rating is changed from 6A to 10A	Marvin
△	06/26'06	Withstanding Voltage is changed from 1.5KV to 1.6KV	Marvin
△	1/31'07	Soldering temperature changed from 245° to 250°	Tony
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal(housing): Thermoplastic (UL94V-0)
- Item ② Contact pin: Brass

Electrical: cULus





- △ ● Voltage rating: 300V
- △ ● Current rating: 10A
- △ ● Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 
- Part No.:

OP xx 22 x x xxxx G

02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

0000: Standard Pb < 40,000ppm
Any special item by (RoHS)
customer request.
please contact sales
department.

0 Tin
1 Gold plating 10u"
2 Gold flash
0 PA66
1 PA46



P.C.B. LAYOUT

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim C	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00	45.50
Dim B	3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00
TOL	±0.10				±0.15				±0.20			
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim C	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	84.00	
Dim B	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	
TOL	±0.25				±0.30				±0.40			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY
FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE
PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OP-3.5mm series										
PART NO.	OPxx22xxxxxxG						DWG NO.	80P0101			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.					Tolerance		
		Jacke 2009.01.05	Jacke 2009.01.05		UNIT: mm			X.	±0.50		
					SCALE: NONE			X.X	±0.30		
					SHEET: 01/01			REV.: F	X.XX	±0.10	
								X°	±1°		