


SIGN	DATE	DESCRIPTION	APPROVER
	06/13/13	Update the drawing	Jacky
<i>THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</i>			



Dimension

DIM A	$N \times 5.0 + 0.10$
DIM B	$(N-1) \times 5.0$

N=Number of poles

POLES	TOL
2p-6p	± 0.20
7p-12p	± 0.30
13p-16p	± 0.35
17p-24p	± 0.40


Material

- Item **a** Terminal body:Thermoplastic (UL94V-0)
- Item **b** Terminal body:Thermoplastic (UL94V-0)
- Item **c** Terminal lever:Thermoplastic (UL94V-0)Orange **A**
- Item **d** Wire guard:Stainless Steel
- Item **e** Male contact pin :PhBz (CuSn) Tin plated



Electrical

- | | |
|--------------------------|--|
| ● Voltage rating: | 300V |
| ● Current rating: | 10A |
| ● Solid wire(AWG): | 12-26 |
| ● Stranded wire(AWG): | 12-26 |
| ● Wire strip length: | 9-10mm |
| ● Withstanding Voltage: | 1.6KV |
| ● Operating temperature: | -40°C to +115°C |
| ● Safety Approval: |  us |
| ● Critical dimension: |  |

cULus



SECTION P-P



H5 xx 70 x 0 xxxx G

02	2 CONTACTS
03	3 CONTACTS
...	...
24	24 CONTACTS

0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7035/D)
△C: GREEN (RAL 6018/U)

0000 Standard @ Logo	RoHS compliant
000A Standard ANY Logo	(lead<4%)
Any special item by customer request,	In copper Alloy
please contact sales department.	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H5 5.0 Series (2P~24P) Without flange						
PART NO.	H5xx70x0xxxxxG			DWG NO.	8H50301A		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacky 2013.06.13	Jacky 2013.06.13		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
					REV.: C	X.XX	±0.10
				SHEET: 01/01		X*	±1*