



德砚电子

DE YAN DIAN ZI

一体成型功率电感

Data Sheet

RoHS



ISO 9001
质量管理体系认证



ISO 14001
环境管理体系认证

Shenzhen Deyan Electronics Co., Ltd


SPECIFICATION

			AMENDMENT RECORD			
SYMBOL	DATE	PAGE	CONTENTS	DWN. BY	CHK. BY	APP. BY
				叶枫	李林	谢东

SPECIFICATION


Customer	Customer P/No.	P/No.	File No.	Date of	Customer Rev.	Rev.	Page of
		D1050HP-6R8MT		2024-11-20	--	01	1/5

1. DIMENSIONS (UNIT : mm)




A	B	C	D	E
10.1±0.3	11.6 Max	5.0 Max.	3.0±0.5	2.5±0.5

2. RECOMMENDED LAND PATTERN (UNIT: mm)



F	13.0 Ref.
G	4.0 Ref.
H	6.0 Ref.

3. STRUCTURE



No.	PARTS	MATERIAL
①	CORE	Alloy powder
②	WIRE	Self bonding polyamide-imide enameled Copper Wire
③	ELECTRODE	Cu
④	MARKING	INK

APPROVAL	CHECK	DESIGN	

SPECIFICATION

Customer	Customer P/No.	P/No.	File No.	Date of	Customer Rev.	Rev.	Page of
		D1050HP-6R8MT		2024-11-20	--	01	2/5

4.CHARACTERISTICS

No.	P/N.	Inductance (μ H)	Stamp	D.C.R. (m Ω) Max.	Saturation Current (A)		Temperature rise current($\Delta T \leq 40^\circ\text{C}$) (A).	
					Typ	MAX	Typ	MAX
01	D1050HP-6R8MT	6.8 $\pm$ 20%	6R8	18.5	12	10	8.0	6.8

* Testing instrument: Inductance HP 4284A or equivalent at 100KHz /1V..

D.C.R : TH2512B or equivalent. ($T_a = 25^\circ\text{C}$)


Saturation current: WK 3260B+3265B or equivalent.

* Saturation Current (I_{sat}) will cause L0 to drop approximately 30% from its value without current.
($T_a = 25^\circ\text{C}$)

* The temperature rise current value is the DC current value having temperature increase up to approximately 40°C ($T_a = 25^\circ\text{C}$)

* Absolute maximum voltage 30VD

6R8 DC Bias & Temperature Characteristics



APPROVAL	CHECK	DESIGN	


SPECIFICATION

Customer	Customer P/No.	P/No.	File No.	Date of	Customer Rev.	Rev.	Page of
		D1050HP-6R8MT		2024-11-20	--	01	3/5
5.GENERAL CHARACTERISTICS * STANDARD TESTING CONDITIONS: UNLESS OTHERWISE SPECIFIED, THE STANDARD RANGE OF ATMOSPHERIC CONDITIONS FOR MEASUREMENTS AND TESTS ARE AS FOLLOWS: AMBIENT TEMPERATURE: 15℃~35℃. RELATIVE HUMIDITY : 25% ~85%. AIR PRESSURE : 86kPa ~106kPa. IF THERE IS ANY DOUBT ABOUT THE RESULTS, MEASUREMENT SHALL BE MADE WITHIN THE FOLLOWING LIMITS: AMBIENT TEMPERATURE: 20℃±1℃. RELATIVE HUMIDITY: 63% ~67%. AIR PRESSURE : 86kPa ~106kPa.							
No.	ITEMS		CONDITIONS		SPECIFICATION		
1	OPERATION TEMPERATURE STORAGE TEMPERATURE				-40 ~ + 125℃ (INCLUDING COIL TEMPERATURE RISE) -40 ~ + 125℃		
2	TEMPERATURE COEFFICIENT		-30 ~ +105℃		0 ~ 2000 ppm/℃		
3	FIXING STRENGTH		SAMPLE IS PUSHED IN THREE DIRECTIONS OF X, Y AND Z WITH FORCE OF 5. 0N FOR 10±5 SECONDS. AFTER SOLDERING BETWEEN COPPER PLATE AND ELECTRODES.		NO ELECTRODE DETACHMENT.		
4	RESISTANCE TO SOLDERING HEAT TEST		REFER TO THE SPEC “STD-001NP”.		NO MECHANICAL BREAKAGE. DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%		
5	SOLDERABILITY TEST		IMMERSE THE ELECTRODE IN FLUX FOR 5 SECONDS. THEN DIP THE ELECTRODE INTO A SOLDERING BATH OF 245±5℃ FOR 2±0.5 SECONDS.		OVER 95% OF THE SURFACE BEING IMMersed SHALL BE COVERED WITH NEW SOLDER UNIFORMLY.		
6	VIBRATION TEST		AMPLITUDE: 1.5mm P-P FREQUENCY:10~55~10Hz (1 MINUTE PER CYCLE) DURATION: 1 HOUR IN EACH OF X, Y, Z AXIS.		DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%		
7	HUMIDITY TEST		TEMPERATURE: 40℃±2℃ HUMIDITY: 90%~95%RH DURATION: 96±4 HOURS.		DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%		
8	THERMAL SHOCK TEST		20 CYCLES OF +105℃ FOR 30 MINUTES, -40℃ FOR 30 MINUTES. CHARACTERISTICS ARE MEASURED AFTER THE AMBIENT AIR EXPOSURE OF 1 HOUR		DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%		
9	HIGH TEMPERATURE STORAGE TEST		TEMPERATURE: 125℃±2℃ DURATION: 96±4 HOURS				
10	LOW TEMPERATURE STORAGE TEST		TEMPERATURE: -40℃±3℃ DURATION: 96±4 HOURS.				
APPROVAL	CHECK	DESIGN					

SPECIFICATION

Customer	Customer P/No.	P/No.	File No.	Date of	Customer Rev.	Rev.	Page of
		D1050HP-6R8MT		2024-11-20	--	01	4/5

6. Reflow profile for SMT components



Reflow is referred to standard IPC/ JEDEC J-STD-020D

Profile Feature		Lead(Pb) Free solder
Preheat and soak	·temperature Min.(Tmin)	150°C
	·temperature Max.(Tmax)	200°C
	·time(Tmin to Tmax)(ts)	60-120 Seconds
Average ramp up rate Tmax to Tp		3°C/Second Max.
Liquidous temperature (TL)		217 °C
Time (TL) maintained above TL		60-150 seconds
Peak package body temperature (Tp)		Table2
Time (tp)* within 5 °C of the specified classification temperature (Tc)		30* seconds
Average Ramp-down rate (Tp to TL)		6 °C/second max
Time 25 °C to peak temperature		8 minutes max.

Table2. Pb-Free Process - Classification Temperatures (Tc)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350~2000	Volume mm ³ >2000
<1.6 mm	260°C	260°C	260°C
1.6mm- 2.5mm	260°C	250°C	245°C
>2.5 mm	250°C	245°C	245°C



APPROVAL	CHECK	DESIGN	

SPECIFICATION

Customer	Customer P/No.	P/No.	File No.	Date of	Customer Rev.	Rev.	Page of
		D1050HP-6R8MT		2024-11-20	--	01	5/5

7. PACKING

REFER TO STANDARD PACKING DRAWING. 500PCS/R



REEL	500PCS
BOX	2500PCS

8. NOTE

SOLDERING TIN PERIOD OF VALIDITY: SIX MONTHS
STORAGE TEMPERATURE: 25°C±5°C
COMPARATIVELY HUMIDITY: 35%--70%

APPROVAL	CHECK	DESIGN	