



S-LBSS139LT1G

Power MOSFET

200 mA, 60 V N-Channel SOT-23

1. FEATURES

- We declare that the material of product compliance with RoHS requirements and Halogen Free.
- S- prefix for automotive and other applications requiring unique site and control change requirements; AEC-Q101 qualified and PPAP capable.
- Low threshold voltage ($V_{GS(th)}$: 0.8V...1.5V) makes it ideal for low voltage applications.
- ESD Protected: 2KV



2. DEVICE MARKING AND ORDERING INFORMATION

Device	Marking	Shipping
S-LBSS139LT1G	J2	3000/Tape&Reel
S-LBSS139LT3G	J2	10000/Tape&Reel

3. MAXIMUM RATINGS($T_a = 25^{\circ}\text{C}$)

Parameter	Symbol	Limits	Unit
Drain-Source Voltage	VDSS	60	V
Gate-to-Source Voltage – Continuous	VGS	± 20	V
Drain Current			mA
– Continuous $T_a = 25^{\circ}\text{C}$	ID	200	
– Pulsed ($t_p \leq 10\mu\text{s}$)	IDM	800	

4. THERMAL CHARACTERISTICS

Parameter	Symbol	Limits	Unit
Total Device Dissipation, FR-4 Board (Note 1) @ $T_a = 25^{\circ}\text{C}$	PD	285	mW
Derate above 25°C		2.3	mW/ $^{\circ}\text{C}$
Thermal Resistance, Junction-to-Ambient(Note 1)	R θ JA	438	$^{\circ}\text{C}/\text{W}$
Junction and Storage temperature	TJ, Tstg	$-55 \sim +150$	$^{\circ}\text{C}$
Maximum Lead Temperature for Solde Purposes, for 10 seconds	TL	260	$^{\circ}\text{C}$

1. 30.0mm×25.0mm×1.6mm(FR4), Copper foil thickness 35 μm ;

5. ELECTRICAL CHARACTERISTICS (Ta= 25°C)

OFF CHARACTERISTICS

Characteristic	Symbol	Min.	Typ.	Max.	Unit
Drain–Source Breakdown Voltage (VGS = 0, ID = 250μA)	VBRDSS	60	-	-	V
Zero Gate Voltage Drain Current (VGS = 0, VDS = 25 V) (VGS = 0, VDS = 50 V)	IDSS	- -	- -	0.1 0.5	μA
Gate–Body Leakage Current, Forward (VGS = 20 Vdc)	IGSSF	-	-	10.0	μA
Gate–Body Leakage Current, Reverse (VGS = - 20 V)	IGSSR	-	-	-10	μA

ON CHARACTERISTICS (Note 2)

Gate Threshold Voltage (VDS = VGS, ID = 1.0mA)	VGS(th)	0.8	-	1.5	V
Static Drain–Source On–State Resistance (VGS = 2.75 V, ID < 200 mA, TA = –40°C to +85°C) (VGS = 5.0 V, ID = 200 mA) (VGS = 10 V, ID = 300 mA)	RDS(on)	- - -	5.6 - -	10 2.0 1.6	Ohms
Forward Transconductance (VDS = 25 V, ID = 200 mA, f = 1.0 kHz)	gfs	100	-	-	mS

DYNAMIC CHARACTERISTICS





Input Capacitance (VDS = 25 V, VGS = 0, f = 1.0 MHz)	Ciss	-	22.8	-	pF
Output Capacitance (VDS = 25 V, VGS = 0, f = 1.0 MHz)	Coss	-	3.5	-	pF
Reverse Transfer Capacitance (VDS = 25 V, VGS = 0, f = 1.0 MHz)	Crss	-	2.9	-	pF

SWITCHING CHARACTERISTICS





Turn-On Delay Time	(VDD = 30 V , VGEN = 10 V, RG =25Ω ,RL =60 Ω, ID =500 mA)	td(on)	-	3.8	-	ns
Turn-Off Delay Time		td(off)	-	19	-	

2.Pulse Test: Pulse Width ≤300 μs, Duty Cycle ≤2.0%.




6. ELECTRICAL CHARACTERISTICS CURVES




6.ELECTRICAL CHARACTERISTICS CURVES(Con.)



7.OUTLINE AND DIMENSIONS



SECTION B-B




SOT23			
DIM	MIN	NOR	MAX
A	0.89	—	1.12
A1	0.01	—	0.10
A2	0.88	0.95	1.02
b	0.30	—	0.50
b1	0.30	0.40	0.45
c	0.08	—	0.20
c1	0.08	0.10	0.16
D	2.80	2.90	3.04
E	2.10	—	2.64
E1	1.20	1.30	1.40
e	0.95BSC		
e1	1.90BSC		
L	0.40	0.46	0.60
L1	0.54REF		
θ	0°	—	8°
All Dimensions in mm			

GENERAL NOTES

- 1.Top package surface finish Ra0.4±0.2um
- 2.Bottom package surface finish Ra0.7±0.2um
- 3.Side package surface finish Ra0.4±0.2um

8.SOLDERING FOOTPRINT



SOT-23	
DIM	(mm)
X	0.80
Y	0.90
A	2.00
B	0.95
C	0.95

DISCLAIMER

- Curve guarantee in the specification. The curve of test items with electric parameter is used as quality guarantee. The curve of test items without electric parameter is used as reference only.
- Before you use our Products for new Project, you are requested to carefully read this document and fully understand its contents. LRC shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any LRC's Products against warning, caution or note contained in this document.
- All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using LRC's Products, please confirm the latest information with a LRC sales representative.