

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
E	B			C1	REVISED PER ECO-11-005150	21MAR11	RK HMR

- NOTES:
1. ELECTRICAL DATA:


CONTACT RESISTANCE: 10 mOhm MAX
INSULATION RESISTANCE: 100 MOhm MIN at 500VDC
CURRENT RATING: 5 AMPS (FOR 3, 4 AND 5 POSITIONS) AND 2 AMPS (FOR 8 POSITION ONLY)
BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE
2. ENVIRONMENTAL:

OPERATING TEMPERATURE: -25°C TO +90°C
SEALING REQUIREMENTS: IP67
3. PROD SPEC:

108-3641
4. PACKAGING:

107-3334
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE.
6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QUANTITY / ITEM			
				-1	-2	-3	-4
1	CONNECTOR HOUSING	GF NYLON	BLACK	1	1	1	1
2	SOCKET CONTACT	BRASS	0.15µm GOLD OVER NICKEL	3	4	5	8
3	CONNECTOR BODY	ZINC DIE CAST	2.5µm NICKEL PLATED	1	1	1	1
4	'O' RING	VITON	GREEN	1	1	1	1
5	'O' RING	EPDM	BLACK	1	1	1	1
6	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1	1	1	1



M12 METAL FEMALE PANEL MOUNT CONNECTOR, SOLDER, STRAIGHT, REAR (HEXAGONAL) MOUNTING	8	1838891-4
M12 METAL FEMALE PANEL MOUNT CONNECTOR, SOLDER, STRAIGHT, REAR (HEXAGONAL) MOUNTING	5	1838891-3
M12 METAL FEMALE PANEL MOUNT CONNECTOR, SOLDER, STRAIGHT, REAR (HEXAGONAL) MOUNTING	4	1838891-2
M12 METAL FEMALE PANEL MOUNT CONNECTOR, SOLDER, STRAIGHT, REAR (HEXAGONAL) MOUNTING	3	1838891-1
DESCRIPTION	NO. OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.Morey	22FEB06	 TE Connectivity		
		CHK F.Wheeler-King	01MAR07			
		APVD F.Wheeler-King	01MAR07	NAME M12 METAL FEMALE PANEL MOUNT CONNECTOR, SOLDER, STRAIGHT, REAR (HEXAGONAL) MOUNTING		
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		WEIGHT —		SIZE A3	CAGE CODE 00779	DRAWING NO C-1838891
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 2	REV C1









4

3

2

1

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	-	SEE SHEET 1		-	-	-

1838891-1	1838891-2	1838891-3	1838891-4
PIN ASSIGNMENTS FRONT VIEW 	PIN ASSIGNMENTS FRONT VIEW 	PIN ASSIGNMENTS FRONT VIEW 	PIN ASSIGNMENTS FRONT VIEW 
RECOMMENDED PANEL CUT-OUT (MAX PANEL THICKNESS 4.5mm) 	RECOMMENDED PANEL CUT-OUT (MAX PANEL THICKNESS 4.5mm) 	RECOMMENDED PANEL CUT-OUT (MAX PANEL THICKNESS 4.5mm) 	RECOMMENDED PANEL CUT-OUT (MAX PANEL THICKNESS 4.5mm) 

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.Morey 28FEB07		TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± -		M12 METAL FEMALE PANEL MOUNT CONNECTOR,		
		1 PLC ± -		SOLDER, STRAIGHT, REAR (CIRCULAR) MOUNTING		
		2 PLC ± -		-		
		3 PLC ± -				
		4 PLC ± -				
		ANGLES ± -				
MATERIAL -		FINISH -		RESTRICTED TO -		